

Type 1 Screw Cover Wireway Fittings - Painted & Galvanized

Catalog Number

45° Elbow									
Catalog Number		A		B		E		F	
Painted	Galvanized	in.	mm	in.	mm	in.	mm	in.	mm
2245 L COMBO	2245 L COMBOGV	2.50	64	2.50	64	1.72	44	1.72	44
3345 L COMBO	3345 L COMBOGV	3.00	76	3.00	76	2.56	65	2.56	65
4445 L COMBO	4445 L COMBOGV	4.00	102	4.00	102	2.75	70	2.75	70
6445 L COMBO	6445 L COMBOGV	4.00	102	6.00	153	2.75	70	2.75	70
6645 L COMBO	6645 L COMBOGV	6.00	153	6.00	153	3.18	81	3.18	81
8845 L COMBO	8845 L COMBOGV	8.00	203	8.00	203	3.62	92	3.62	92
101045 L COMBO	101045 L COMBOGV	10.00	254	10.00	254	4.06	103	4.06	103
121245 L COMBO	121245 L COMBOGV	12.00	305	12.00	305	4.50	114	4.50	114
2245 L SIDE	2245 L SIDE GV	2.50	64	2.50	64	1.97	50	1.97	50
3345 L SIDE	3345 L SIDE GV	3.00	76	3.00	76	2.56	65	2.56	65
4445 L SIDE	4445 L SIDE GV	4.00	102	4.00	102	2.75	70	2.75	70
6445 L SIDE	6445 L SIDE GV	6.00	153	4.00	102	3.18	81	3.18	81
6645 L SIDE	6645 L SIDE GV	6.00	153	6.00	153	3.18	81	3.18	81
8845 L SIDE	8845 L SIDE GV	8.00	203	8.00	203	3.62	92	3.62	92
101045 L SIDE	101045 L SIDE GV	10.00	254	10.00	254	4.06	103	4.06	103
121245 L SIDE	121245 L SIDE GV	12.00	305	12.00	305	4.50	114	4.50	114

Tee									
Catalog Number		A		B		E		F	
Painted	Galvanized	in.	mm	in.	mm	in.	mm	in.	mm
22 T	22 TGV	2.50	64	2.50	64	4.25	108	4.25	108
33 T	33 TGV	3.00	76	3.00	76	4.50	114	4.50	114
44 T	44 TGV	4.00	102	4.00	102	5.00	127	5.00	127
64 T	64 TGV	6.00	153	4.00	102	7.00	178	7.00	178
66 T	66 TGV	6.00	153	6.00	153	7.00	178	7.00	178
88 T	88 TGV	8.00	203	8.00	203	8.00	203	8.00	203
1010 T	1010 TGV	10.00	254	10.00	254	9.00	229	9.00	229
1212 T	1212 TGV	12.00	305	12.00	305	10.00	254	10.00	254

Cross									
Catalog Number		A		B		E		F	
Painted	Galvanized	in.	mm	in.	mm	in.	mm	in.	mm
22 X	22 XGV	2.50	64	2.50	64	4.25	108	4.25	108
33 X	33 XGV	3.00	76	3.00	76	5.62	143	5.62	143
44 X	44 XGV	4.00	102	4.00	102	6.12	155	6.12	155
64 X	64 XGV	6.00	152	4.00	152	7.12	181	7.12	181
66 X	66 XGV	6.00	152	6.00	152	7.12	181	7.12	181
88 X	88 XGV	8.00	203	8.00	203	8.12	206	8.12	206
1010 X	1010 XGV	10.00	254	10.00	254	9.12	232	9.12	232
1212 X	1212 XGV	12.00	305	12.00	305	10.12	257	10.12	257

Barrier Kit, 60" Bolt-On						
Catalog Number	Size		Length		H	
	in.	mm	in.	mm	in.	mm
22-12BK*	2.50x2.50	64x64	60.00	1524	1.88	48
33-12BK*	3.00x3.00	76x76	60.00	1524	2.25	57
44-12BK*	4.00x4.00	102x102	60.00	1524	3.00	76
66-12BK*	6.00x6.00	152x152	60.00	1524	4.50	114
88-12BK*	8.00x8.00	203x203	60.00	1524	6.00	152
1010-12BK*	10.00x10.00	254x254	60.00	1524	8.00	203
1212-12BK*	12.00x12.00	305x305	60.00	1524	10.50	267

*Not UL or CSA listed fitting.

Type 1 Wireway Competitor Adapters							
Wireway Size		Hoffman ^{®1}	Wiegmann ^{®2}	Square D ^{®3}	Unity ^{®4}	Electrical Box and Enclosures ^{®5}	Austin ^{®6}
in.	mm						
2.5x2.5	64x64	22 CA	22 CA	22 CA	22 CA	-	22 ACA
4x4	102x102	44 CA	44 CA	44 CA	44 CA	44 CA	44 ACA
6x6	152x152	66 CA	66 CA	66 CA	66 CA	66 CA	66 ACA
8x8	203x203	88 CA	88 CA	88 SCA	88 CA	88 CA	88 ACA
10x10	254x254	1010 CA	1010 CA	1010 SCA	1010 CA	1010 CA	1010 ACA
12x12	305x305	1212 CA	1212 CA	1212 SCA	1212 CA	1212 CA	1212 ACA

1. HOFFMAN[®] is the registered trademark of Hoffman Engineering Company, Anoka, Minnesota.
2. WIEGMANN[®] is the registered trademark of Hubbell Incorporated, Orange, Connecticut.
3. SQUARE D[®] is the registered trademark of Square D Company, Palatine, Illinois.
4. UNITY[®] is the registered trademark of Unity Manufacturing, Garland, Texas.
5. ELECTRICAL BOX AND ENCLOSURES[®] is the registered trademark of Electrical Box and Enclosures, Alabaster, Alabama.
6. AUSTIN[®] is the registered trademark of The Austin Co., Yadkinville, North Carolina.

Notes: Dimensions are in inches. Millimeters shown are for reference only. Data subject to change without notice.