

## Feed-Through Wireway Type 12 Data Sheet



### Application

- Houses runs of control and power cable
- Protects against circulating dust, falling dirt and dripping noncorrosive liquids

### Standards

- UL 870 listed, unless noted, (see table)
- CSA C22.2 No. 26 certified, unless noted, (see table)
- Conforms to NEMA standard for Type 12
- Conforms to JIC standard EGP-1-1967

### Finish

- Wash and phosphate undercoat
- ANSI 61 gray polyester powder finish
- Hardware and latches are zinc plated

### Accessories

- Touch-up paint
- See Accessories section

### Construction

- Wireway body and cover are fabricated from (14) gauge steel
- Flanges are (10) gauge steel
- All continuous welded seams are finished smooth
- External and internal edges are rounded to prevent injury or damage to cable
- Covers are secured to the wireway body with heavy-duty hinges on one side and easy-to-operate screw clamps mounted to the opposite side
- Continuous flanged ends assure rigid connections of wireway and fittings
- Covers have a seamless poured in-place gasket
- An oil-resistant gasket is provided for installation between flanges

### Discount Schedule: C2

### Subclass: DAO

**Notes:** Cooper B-Line Systems can provide special sizes, finishes and other modifications. Consult the factory for your special requirements.