

Type 1 Screw Cover Wireway - Painted & Galvanized Catalog Number

Wireway Catalog Number				Wireway Size		D		Gauge	Knockout Quantity	
Painted		Galvanized		Height x Depth x Length A x B x C		in.	mm		Top	Bottom
KO	No KO	KO	No KO	in.	mm					
2212 G	2212 G NK	2212 GGV	2212 GGV NK	2.50x2.50x12.00	64x64x305	1.25	32	16	3	3
2218 G	2218 G NK	2218 GGV	2218 GGV NK	2.50x2.50x18.00	64x64x457	1.25	32	16	5	5
2224 G	2224 G NK	2224 GGV	2224 GGV NK	2.50x2.50x24.00	64x64x610	1.25	32	16	7	7
2236 G	2236 G NK	2236 GGV	2236 GGV NK	2.50x2.50x36.00	64x64x914	1.25	32	16	11	11
2248 G	2248 G NK	2248 GGV	2248 GGV NK	2.50x2.50x48.00	64x64x1219	1.25	32	16	15	15
2260 G	2260 G NK	2260 GGV	2260 GGV NK	2.50x2.50x60.00	64x64x1524	1.25	32	16	19	19
2272 G	2272 G NK	2272 GGV	2272 GGV NK	2.50x2.50x72.00	64x64x1829	1.25	32	16	23	23
22120 G	22120 G NK	22120 GGV	22120 GGV NK	2.50x2.50x120.00	64x64x3048	1.25	32	16	39	39
3312 G	3312 G NK	3312 GGV	3312 GGV NK	3.00x3.00x12.00	76x76x305	1.50	38	16	3	3
3318 G	3318 G NK	3318 GGV	3318 GGV NK	3.00x3.00x18.00	76x76x457	1.50	38	16	5	5
3324 G	3324 G NK	3324 GGV	3324 GGV NK	3.00x3.00x24.00	76x76x610	1.50	38	16	7	7
3336 G	3336 G NK	3336 GGV	3336 GGV NK	3.00x3.00x36.00	76x76x914	1.50	38	16	11	11
3348 G	3348 G NK	3348 GGV	3348 GGV NK	3.00x3.00x48.00	76x76x1219	1.50	38	16	15	15
3360 G	3360 G NK	3360 GGV	3360 GGV NK	3.00x3.00x60.00	76x76x1524	1.50	38	16	19	19
3372 G	3372 G NK	3372 GGV	3372 GGV NK	3.00x3.00x72.00	76x76x1829	1.50	38	16	23	23
33120 G	33120 G NK	33120 GGV	33120 GGV NK	3.00x3.00x120.00	76x76x3048	1.50	38	16	39	39
4412 G	4412 G NK	4412 GGV	4412 GGV NK	4.00x4.00x12.00	102x102x305	2.75	70	16	3	3
4418 G	4418 G NK	4418 GGV	4418 GGV NK	4.00x4.00x18.00	102x102x457	2.75	70	16	5	5
4424 G	4424 G NK	4424 GGV	4424 GGV NK	4.00x4.00x24.00	102x102x610	2.75	70	16	7	7
4436 G	4436 G NK	4436 GGV	4436 GGV NK	4.00x4.00x36.00	102x102x914	2.75	70	16	11	11
4448 G	4448 G NK	4448 GGV	4448 GGV NK	4.00x4.00x48.00	102x102x1219	2.75	70	16	15	15
4460 G	4460 G NK	4460 GGV	4460 GGV NK	4.00x4.00x60.00	102x102x1524	2.75	70	16	19	19
4472 G	4472 G NK	4472 GGV	4472 GGV NK	4.00x4.00x72.00	102x102x1829	2.75	70	16	23	23
44120 G	44120 G NK	44120 GGV	44120 GGV NK	4.00x4.00x120.00	102x102x3048	2.75	70	16	39	39
6412 G	6412 G NK	6412 GGV	6412 GGV NK	6.00x4.00x12.00	152x102x305	4.25	108	16	3	3
6418 G	6418 G NK	6418 GGV	6418 GGV NK	6.00x4.00x18.00	152x102x457	4.25	108	16	5	5
6424 G	6424 G NK	6424 GGV	6424 GGV NK	6.00x4.00x24.00	152x102x610	4.25	108	16	7	7
6436 G	6436 G NK	6436 GGV	6436 GGV NK	6.00x4.00x36.00	152x102x914	4.25	108	16	11	11
6448 G	6448 G NK	6448 GGV	6448 GGV NK	6.00x4.00x48.00	152x102x1219	4.25	108	16	15	15
6460 G	6460 G NK	6460 GGV	6460 GGV NK	6.00x4.00x60.00	152x102x1524	4.25	108	16	19	19
6472 G	6472 G NK	6472 GGV	6472 GGV NK	6.00x4.00x72.00	152x102x1829	4.25	108	16	23	23
64120 G	64120 G NK	64120 GGV	64120 GGV NK	6.00x4.00x120.00	152x102x3048	4.25	108	16	39	39
6612 G	6612 G NK	6612 GGV	6612 GGV NK	6.00x6.00x12.00	152x152x305	4.25	108	16	3	3
6618 G	6618 G NK	6618 GGV	6618 GGV NK	6.00x6.00x18.00	152x152x457	4.25	108	16	5	5
6624 G	6624 G NK	6624 GGV	6624 GGV NK	6.00x6.00x24.00	152x152x610	4.25	108	16	7	7
6636 G	6636 G NK	6636 GGV	6636 GGV NK	6.00x6.00x36.00	152x152x914	4.25	108	16	11	11
6648 G	6648 G NK	6648 GGV	6648 GGV NK	6.00x6.00x48.00	152x152x1219	4.25	108	16	15	15
6660 G	6660 G NK	6660 GGV	6660 GGV NK	6.00x6.00x60.00	152x152x1524	4.25	108	16	19	19
6672 G	6672 G NK	6672 GGV	6672 GGV NK	6.00x6.00x72.00	152x152x1829	4.25	108	16	23	23
66120 G	66120 G NK	66120 GGV	66120 GGV NK	6.00x6.00x120.00	152x152x3048	4.25	108	16	39	39

See page 14 for 8"x8" through 12"x12" wireway.

Notes: Dimensions are in inches. Millimeters shown are for reference only. Data subject to change without notice.