

Type 1 Screw Cover Wireway - Painted & Galvanized Catalog Number

Wireway Catalog Number				Wireway Size		D		Gauge	Knockout Quantity	
Painted		Galvanized		Height x Depth x Length A x B x C		in.	mm		Top	Bottom
KO	No KO	KO	No KO	in.	mm					
8812 G	8812 G NK	8812 GGV	8812 GGV NK	8.00x8.00x12.00	203x203x305	6.00	152	14	3	3
8818 G	8818 G NK	8818 GGV	8818 GGV NK	8.00x8.00x18.00	203x203x457	6.00	152	14	5	5
8824 G	8824 G NK	8824 GGV	8824 GGV NK	8.00x8.00x24.00	203x203x610	6.00	152	14	7	7
8836 G	8836 G NK	8836 GGV	8836 GGV NK	8.00x8.00x36.00	203x203x914	6.00	152	14	11	11
8848 G	8848 G NK	8848 GGV	8848 GGV NK	8.00x8.00x48.00	203x203x1219	6.00	152	14	15	15
8860 G	8860 G NK	8860 GGV	8860 GGV NK	8.00x8.00x60.00	203x203x1524	6.00	152	14	19	19
8872 G	8872 G NK	8872 GGV	8872 GGV NK	8.00x8.00x72.00	203x203x1829	6.00	152	14	23	23
88120 G	88120 G NK	88120 GGV	88120 GGV NK	8.00x8.00x120.00	203x203x3048	6.00	152	14	39	39
101012 G	101012 G NK	101012 GGV	101012 GGV NK	10.00x10.00x12.00	254x254x305	8.00	203	14	3	3
101024 G	101024 G NK	101024 GGV	101024 GGV NK	10.00x10.00x24.00	254x254x610	8.00	203	14	7	7
101036 G	101036 G NK	101036 GGV	101036 GGV NK	10.00x10.00x36.00	24x254x914	8.00	203	14	11	11
101048 G	101048 G NK	101048 GGV	101048 GGV NK	10.00x10.00x48.00	254x254x1219	8.00	203	14	15	15
101060 G	101060 G NK	101060 GGV	101060 GGV NK	10.00x10.00x60.00	254x254x1524	8.00	203	14	19	19
101072 G	101072 G NK	101072 GGV	101072 GGV NK	10.00x10.00x72.00	254x254x1829	8.00	203	14	23	23
1010120 G	1010120 G NK	1010120 GGV	1010120 GGV NK	10.00x10.00x120.00	254x254x3048	8.00	203	14	39	39
121212 G	121212 G NK	121212 GGV	121212 GGV NK	12.00x12.00x12.00	305x305x305	10.00	254	14	3	3
121224 G	121224 G NK	121224 GGV	121224 GGV NK	12.00x12.00x24.00	305x305x610	10.00	254	14	7	7
121236 G	121236 G NK	121236 GGV	121236 GGV NK	12.00x12.00x36.00	305x305x914	10.00	254	14	11	11
121248 G	121248 G NK	121248 GGV	121248 GGV NK	12.00x12.00x48.00	305x305x1219	10.00	254	14	15	15
121260 G	121260 G NK	121260 GGV	121260 GGV NK	12.00x12.00x60.00	305x305x1524	10.00	254	14	19	19
121272 G	121272 G NK	121272 GGV	121272 GGV NK	12.00x12.00x72.00	305x305x1829	10.00	254	14	23	23
1212120 G	1212120 G NK	1212120 GGV	1212120 GGV NK	12.00x12.00x120.00	305x305x3048	10.00	254	14	39	39

Notes: Dimensions are in inches. Millimeters shown are for reference only. Data subject to change without notice.