



Dependable Power for Any Application

# Product Datasheet

## 460Δ Primary Volts - 230Y/133 Secondary Volts - 3Ø Drive Isolation Transformer - Three Phase

Catalog #: DTGA0112S



### PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Aluminum foil windings
- Copper wire terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79911

---

### BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

---

### UL STANDARD

UL 506

---

### CSA STANDARD

C22.2 No. 47

---

### WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

kVA:	11.00
Primary Voltage:	460Δ
Secondary Voltage:	230Y/133
Frequency:	60 Hz
ANFC Taps:	1
BNFC Taps:	1
Taps % Steps:	5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

## PRODUCT MEASUREMENTS

Height (In./cm):	18.86 (47.9)
Width (In./cm):	20.3 (51.6)
Depth (In./cm):	9.03 (22.9)

## CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor
Wiring Diagram:	62

## PACKAGING

Ship Weight (Lbs/Kg):	265 (120.0)
-----------------------	-------------

## COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card <a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>

