



Dependable Power for Any Application

# Product Datasheet

Autotransformer - 600/480 Primary Volts - 480/380 Secondary Volts - 3Ø

Dry Type Distribution Transformer - Three Phase

Catalog #: T2527071



## PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

## BENEFITS

- Quiet operation with sound levels below NEMA standards

---

## UL STANDARD

- UL 506

---

## CSA STANDARD

- C22.2 No. 47

---

## WARRANTY

- Acme Electric Warranty Card
- [www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

---

## GENERAL PRODUCT INFORMATION

kVA:	45/36
Primary Voltage:	600/480
Secondary Voltage:	480/380
Frequency:	50/60 Hz
ANFC Taps:	-
BNFC Taps:	2
Taps % Steps:	5.0%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

#### PRODUCT MEASUREMENTS

Height (In./cm):	15.21 (38.6)
Width (In./cm):	19.25 (48.9)
Depth (In./cm):	7.37 (18.7)

#### CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Wiring Diagram:	56

#### PACKAGING

Ship Weight (Lbs/Kg):	156 (70.8)
-----------------------	------------

#### COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>	