



Representative

Catalog Number: ICS77-1
Product ID: 7TAA267180R0024
UPC Number: 78378610249
Status: Active

Aluminum 2-25/32 inch Service Entrance Compression Splice for Wire Range - End A: 1/0 ASCR, 1/0, Yellow, End B: 2 ASCR, 1-2 Stranded, Red, Die: 5/8

North American Specifications (UNSPSC)

| | |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| UNSPSC | 39121449 Wire or cable compression splice |
| IGCC | 4669 Wire or cable compression splice |
| Brand Name | Blackburn |
| Type | Service Entrance Splices |
| Special Features | Constructed from Aluminum for High Conductivity. Solid Center Barriers and large Chamfers for easy cable insertion. Tough Stabilized nylon sleeves resist installing tool Pressure and provide Reliable 600 V Insulation. Prefilled with Oxide Inhibitor to prevent Oxidation and keep out moisture. All Splices are Color Coded and Marked with trip lengths, Installation Die Codes and Compression Locations, Providing easy Identification for easy Installation. Splices have Colored End Caps to make Identification easy. |
| Application | For Standard Conductor Splice. |
| Standard | RUS Accepted. Complies with ANSI C119.4 when properly installed on Aluminum-to-Aluminum or Aluminum-to-Copper Conductors. |
| Size | 2-25/32 inch |
| Connection | Crimp/ Compression |
| Conductor Range | End A: 1/0 ASCR, 1/0, End B: 2 ASCR, 1-2 Stranded. |
| Number Of Conductors | 2 |
| Material | Aluminum |
| Insulation | Yes |
| Mounting | None |
| Environmental Conditions | All Seasons / Conditions |

Packaging

| | |
|---------------------------|------------------|
| Inner Quantity | 100 |
| Inner Dimensions (inches) | 10.5x7.3x3.7 |
| Outer Quantity | 500 |
| Outer Dimensions (inches) | 20.29x10.9x7.9 |
| Weight Uom | 4.5 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com