

**Catalog Number:** W62-1FC  
**Product ID:** 7TAA267150R0021  
**UPC Number:** 78378633201  
**EAN Number:** 05415022349252  
**Status:** Active



Representative

Aluminum Service Entrance Wedge Clamp and Slider for Wire Range: 2-6 ASCR, 2-6 AAAC, 1 Str.-6 Sol. Flexible Bail, Color Code Orange

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	Blackburn
Type	Aluminum Service Wedge Clamp
Special Features	Drop wire may be cut to exact length for adjustments in drop wire sag. Can be attached to bare neutral at any point in the span. Flexible and rigid bails grip ACSR, AAC and AAAC Conductors.
Application	Dead-End Self-supporting Drop Wire
Size	Length 12-1/2 inches X Depth Flexible
Conductor Range	2-6 ASCR, 2-6 AAAC, 1 Str.-6 Sol.
Number Of Conductors	1
Material	Aluminum
Finish	Bare
Voltage Rating	35kV
Insulation	None
Mounting	Yes
Connection	Tension
Environmental Conditions	All Seasons / Conditions

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	13.7x8.5x8.5
Weight Uom	14.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com