

Meter Mains - With Safety Socket Bypass

100 Amp - Fusible Pullout



U214 MTBP (open)

214 MTBP (open)

Application

- Combination meter/main with safety socket (test block) bypass
- Factory installed fused pullout ("T" fuses included)
- Receive ANSI C12.10 watt-hour meters
- Surface mount

Construction

- Ring type
- NEMA Type 3R
- ANSI 61 gray E-coat finish
- Aluminum snap ring included



Standards

- UL 67 Listed
- ANSI C12.7
- EUSERC 305A

Accessories

- 5th Jaw Kit - 50371
- Bussed Gutters - see page 51
- AW Hubs

Single Meter Sockets
With Safety Socket Bypass

Part/UPC Number	Catalog Number	Amp Rating	Jaws	Service Type	Access	Main Breaker		Main	Bypass
						Voltage	AIC		
78205148000	214 MTBP	100	4	1Ø/3W	OH	120/240	200K	(1) 100A, 2P	TB
78205152000	214 MTBP MS15	100	4	1Ø/3W	OH	240/480	200K	(1) 100A, 2P	TB
78205148020	215 MTBP	100	5	3Ø/3W	OH	240*	200K	(1) 100A, 3P	TB
78205152010	215 MTBP MS15	100	5	3Ø/3W	OH	480*	200K	(1) 100A, 3P	TB
78205148030	217 MTBP	100	7	3Ø/4W	OH	120/240 & 120/208	200K	(1) 100A, 3P	TB
78205152020	217 MTBP MS15	100	7	3Ø/4W	OH	480/277	200K	(1) 100A, 3P	TB
78205148080	U214 MTBP	100	4	1Ø/2W	OH/UG	120/240	200K	(1) 100A, 2P	TB
78205152060	U214 MTBP MS15	100	4	1Ø/2W	OH/UG	240/480	200K	(1) 100A, 2P	TB
78205148100	U215 MTBP	100	5	3Ø/3W	OH/UG	240*	200K	(1) 100A, 3P	TB
78205152070	U215 MTBP MS15	100	5	3Ø/3W	OH/UG	480*	200K	(1) 100A, 3P	TB
78205148110	U217 MTBP	100	7	3Ø/4W	OH/UG	120/240 & 120/208	200K	(1) 100A, 3P	TB
78205152100	U217 MTBP MS15	100	7	3Ø/4W	OH/UG	480/277	200K	(1) 100A, 3P	TB

* For a 208/120V, 1Ø/3W system, order a 4-jaw unit and a 5th jaw kit

Part/UPC Number	Catalog Number	Connections			Overall Dimensions			Top Provision	Knockout Layout
		Line	Load	Neutral	Height	Width	Depth		
78205148000	214 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205152000	214 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205148020	215 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205152010	215 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205148030	217 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205152020	217 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	38"	12"	4 ⁵ / ₈ "	AW Hub	Fig. 1
78205148080	U214 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2
78205152060	U214 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2
78205148100	U215 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2
78205152070	U215 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2
78205148110	U217 MTBP	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2
78205152100	U217 MTBP MS15	#14 - 2/0	Main Fuse	#14 - 1/0	24"	18"	4 ⁵ / ₈ "	AW Hub	Fig. 2