

## General Purpose Three Phase, 60 Hz

Type	Pri Sec KVA	208 - 208Y/120 Electrostatically Shielded	208 480Y/277	240 208Y/120 Electrostatically Shielded	440 220Y/127	480 208Y/120	480 - 208Y/120 Electrostatically Shielded
FB	3			TE242D3FS		TE4D3F	TE4D3FS
	6			TE242D6FS		TE4D6F	TE4D6FS
	9			TE242D9FS		TE4D9F	TE4D9FS
	15			TE242D15FS		TE4D15F	TE4D15FS
FH	15	T202H15SE	T204H15E	T242T15SE	T422X15E	T4T15E	T4T15SE
	30	T202H30SE	T204H30E	T242T30SE		T4T30E	T4T30SE
	45	T202H45SE	T204H45E	T242T45SE		T4T45E	T4T45SE
	75	T202H75SE	T204H75E	T242T75SE	T422X75E	T4T75E	T4T75SE
	112.5	T202H112SE	T204H112E	T242T112SE		T4T112E	T4T112SE
	150	T202H150SE	T204H150E	T242T150SE		T4T150E	T4T150SE
	225	T202J225SE	T204J225E	T242J225SE		T4T225E	T4T225SE
	300	T202L300SE	T204L300E	T242L300SE		T4T300E	T4T300SE
	500	T202E500SE	T204E500E	T242B500SE		T4T500E	T4T500SE
	750		T204E750E			T4T750E	T4T750SE
1000					T4J1000E	T4J1000SE	

## 115° C Optional Temperature Rise

FH	15	T202H15FSE	T204H15FE	T242T15FSE		T4T15FE	T4T15FSE
	30	T202H30FSE	T204H30FE	T242T30FSE		T4T30FE	T4T30FSE
	45	T202H45FSE	T204H45FE	T242T45FSE		T4T45FE	T4T45FSE
	75	T202H75FSE	T204H75FE	T242T75FSE		T4T75FE	T4T75FSE
	112.5	T202H112FSE	T204H112FE	T242T112FSE		T4T112FE	T4T112FSE
	150	T202J150FSE	T204J150FE	T242J150FSE		T4T150FE	T4T150FSE
	225	T202L225FSE	T204L225FE	T242L225FSE		T4T225FE	T4T225FSE
	300	T202B300FSE	T204B300FE	T242B300FSE		T4T300FE	T4T300FSE
	500		T204E500FE			T4T500FE	T4T500FSE

## 80° C Optional Temperature Rise

FH	15	T202H15BSE	T204H15BE	T242T15BSE		T4T15BE	T4T15BSE
	30	T202H30BSE	T204H30BE	T242T30BSE		T4T30BE	T4T30BSE
	45	T202H45BSE	T204H45BE	T242T45BSE		T4T45BE	T4T45BSE
	75	T202H75BSE	T204H75BE	T242T75BSE		T4T75BE	T4T75BSE
	112.5	T202J112BSE	T204J112BE	T242T112BSE		T4T112BE	T4T112BSE
	150	T202J150BSE	T204J150BE	T242J150BSE		T4T150BE	T4T150BSE
	225	T202B225BSE	T204B225BE	T242B225BSE		T4T225BE	T4T225BSE
	300	T202B300BSE	T204B300BE	T242B300BSE		T4T300BE	T4T300BSE
	500		T204E500BE			T4T500BE	T4T500BSE