

Cooper Bussmann Part Number	Volt	Amp	Type		Weight kg
170M5744	1250	500	2FKE/115	aR	0,740
170M5745	1250	550	2FKE/115	aR	0,740
170M5746	1250	630	2FKE/115	aR	0,740
170M5747	1100	700	2FKE/115	aR	0,740
170M5748	1100	800	2FKE/115	aR	0,740
170M5749	1000	900	2FKE/115	aR	0,740
170M5750	1000	1000	2FKE/115	aR	0,740
170M5758	660	400	2FKE/115	aR	0,625
170M5759	660	450	2FKE/115	aR	0,625
170M5760	660	500	2FKE/115	aR	0,625
170M5761	660	550	2FKE/115	aR	0,625
170M5762	660	630	2FKE/115	aR	0,625
170M5763	660	700	2FKE/115	aR	0,625
170M5764	660	800	2FKE/115	aR	0,625
170M5765	660	900	2FKE/115	aR	0,625
170M5766	660	1000	2FKE/115	aR	0,625
170M5767	660	1100	2FKE/115	aR	0,625
170M5768	660	1250	2FKE/115	aR	0,625
170M5776	660	900	2FKE/115		0,625
170M5804	660	200	DIN 2	aR	0,600
170M5805	660	250	DIN 2	aR	0,600
170M5806	660	315	DIN 2	aR	0,600
170M5807	660	350	DIN 2	aR	0,600
170M5808	660	400	DIN 2	aR	0,600
170M5809	660	450	DIN 2	aR	0,600
170M5810	660	500	DIN 2	aR	0,600
170M5811	660	550	DIN 2	aR	0,600
170M5812	660	630	DIN 2	aR	0,600
170M5813	660	700	DIN 2	aR	0,600
170M6008	660	500	3/80	aR	0,830
170M6009	660	550	3/80	aR	0,830
170M6010	660	630	3/80	aR	0,830
170M6011	660	700	3/80	aR	0,830
170M6012	660	800	3/80	aR	0,830
170M6013	660	900	3/80	aR	0,830
170M6014	660	1000	3/80	aR	0,830
170M6015	660	1100	3/80	aR	0,830
170M6016	660	1250	3/80	aR	0,830
170M6017	660	1400	3/80	aR	0,830
170M6018	660	1500	3/80	aR	0,830
170M6019	660	1600	3/80	aR	0,830
170M6020	600	1800	3/80	aR	0,830
170M6021	550	2000	3/80	aR	0,830
170M6035	690	700	3STN/110		0,905
170M6058	660	500	3T/80	aR	0,830
170M6059	660	550	3T/80	aR	0,830
170M6060	660	630	3T/80	aR	0,830
170M6061	660	700	3T/80	aR	0,830
170M6062	660	800	3T/80	aR	0,830