

Cooper Bussmann Part Number	Volt	Amp	Type	Weight kg
170L4926	660	50	00T/80	0,250
170L4928	660	63	00T/80	0,250
170L4934	660	80	00T/80	0,250
170L4941	660	200	1*K/110	0,290
170L4942	660	250	1*K/110	0,290
170L4948	660	200	1*B/50	0,250
170L4953	660	160	1*BT/50	0,250
170L4955	660	250	1*BT/50	0,250
170L4956	660	80	1*BK/50	0,250
170L4957	660	100	1*BK/50	0,250
170L4958	660	125	1*BK/50	0,250
170L4959	660	160	1*BK/50	0,250
170L4960	660	200	1*BK/50	0,250
170L4961	660	250	1*BK/50	0,250
170L4977	660	200	1*ST/110	0,430
170L4978	660	80	1*EK/76	0,290
170L4979	660	100	1*EK/76	0,290
170L4980	660	125	1*EK/76	0,290
170L4982	660	160	1*EK/76	0,290
170L4983	660	200	1*EK/76	0,290
170L4985	660	315	1*/80	0,400
170L5007	1000	250	1B/75	0,650
170L5015	1000	315	1B/75	0,650
170L5020	660	250	1*ST/110	0,430
170L5021	1000	250	1BK/75	0,650
170L5022	1000	315	1BK/75	0,650
170L5023	1000	350	1BK/75	0,650
170L5024	1000	400	1BK/75	0,650
170L5025	1000	450	1BK/75	0,650
170L5026	1000	500	1BK/75	0,650
170L5101	660	350	1ST/110	0,650
170L5102	660	400	1ST/110	0,650
170L5104	660	315	1*K/80	0,290
170L5121	1600	160	1KN/140	0
170L5151	1000	315	1BK/80	0,650
170L5160	1000	500	1BK/80	0,650
170L5186	660	315	1/80	0,400
170L5188	660	400	1/80	0,400
170L5189	660	450	1/80	0,400
170L5190	660	500	1/80	0,400
170L5191	660	630	1/80	0,400
170L5194	1000	250	1/110	0,650
170L5195	1000	315	1/110	0,650
170L5196	1000	350	1/110	0,650
170L5197	1000	400	1/110	0,650
170L5198	1000	450	1/110	0,650
170L5199	1000	500	1/110	0,650
170L5210	660	250	1BK/50	0,400
170L5227	660	350	1T/80	0,400