

UL 98 Non-Fused Rotary Disconnect Switches—100, 200 and 400A

For a Complete Assembly, Please Select:

SWITCH + LUGS		Switch								
		Switch Amp Rating	No. of Poles	SCCR	Max Horsepower Rating				Part Number	
					1-Phase 220/240Vac	220/240Vac	3-Phase 440/480Vac	600 Vac		
		100	3	200kA	10	30	75	100	RD100-3-SCCR	
		200	3	200kA	10	75	150	200	RD200-3	
		200	4	200kA	10	75	150	200	RD200-4	
		400	3	200kA	-	125	250	350	RD400-3	
		400	4	200kA	-	125	250	350	RD400-4	
		Terminal Lug Kit								
		Switch Amp Rating	No. of Poles	Lugs Per Kit	Wire Range			Wire Type	Part Number	
100-200	2	2	#6-300MCM			75°C Cu/Al	LUG1-2			
100-200	3	3	#6-300MCM			75°C Cu/Al	LUG1-3			
100-200	4	4	#6-300MCM			75°C Cu/Al	LUG1-4			
400	2	2	#4-600MCM or Dual 1/0-250MCM			75°C Cu/Al	LUG2-2			
400	3	3	#4-600MCM or Dual 1/0-250MCM			75°C Cu/Al	LUG2-3			
400	4	4	#4-600MCM or Dual 1/0-250MCM			75°C Cu/Al	LUG2-4			
400	2	2	(2) #6-350MCM			75°C Cu/Al	LUG3-2			
400	3	3	(2) #6-350MCM			75°C Cu/Al	LUG3-3			
400	4	4	(2) #6-350MCM			75°C Cu/Al	LUG3-4			
SELECT FOR STANDARD APPLICATIONS		Direct Mount Handle - mounts directly to switch, no shaft required								
		For Switch Part Number	Color	Test Function	Padlockable				Part Number	
	All Switches	Black	N	Y				DIR-03		
	OR									
	HANDLE		External Front Operated Pistol Handles - shaft required							
			NEMA Type	Color	Test Function	Padlockable	Defeatable			Part Number
			1, 3R, 12	Black	N	Y	Y			H12-03B
			1, 3R, 12	Red/Yellow	N	Y	Y			H12-03R
			1, 3R, 4, 4X, 12	Black	N	Y	Y			H4X-06B
			1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y			H4X-06R
Metalic Hasp (Heavy Duty) External Front Operated Pistol Handles - shaft required										
NEMA Type			Color	Test Function	Padlockable	Defeatable			Part Number	
1, 3R, 4, 4X, 12			Black	N	Y	Y			H4X-06BHD	
1, 3R, 4, 4X, 12			Red/Yellow	N	Y	Y			H4X-06RHD	
ACCESSORIES		Shafts for Pistol Handles								
		Length in (mm)	Mounting Depth (X) in (mm)					Part Number		
		7.9 (200)	5.31~10.43 (135~265)					SH5-200		
		12.6 (320)	5.31~15.16 (135~385)					SH5-320		
		15.7 (400)	5.31~18.31 (135~465)					SH5-400		
		Shaft Guide								
		Required for 15.7" (400mm) long shafts, optional for other lengths							Part Number	
									SH-GUIDE2	
		and ...								
		ACCESSORIES		Auxiliary Contacts						
Contact Type	Number of Contacts			Continuous Amp Rating	Voltage Rating	Max Number of Aux Contacts per Switch	Part Number			
NO + NC	1 of each			10.1A	125-250Vac	2	BAC03*			
NO + NC	1 of each			10.1A	125-250Vac	2	BAC04*			
NO + NC	1 of each			1A	125Vac	2	BAC11*			
NO + NC	1 of each	1A	125Vac	2	BAC12*					
* For one auxiliary contact, install either BAC03 or BAC11. For two auxiliary contacts, install BAC03 + BAC04, or BAC11 + BAC12.										