

# UL 98 Fused Rotary Disconnect Switches—30A

## Compact Class CC & Class J

For a Complete Assembly, Please Select:

SWITCH		<b>Switch</b>									
		<b>Amp Rating</b>	<b>Fuse Class</b>	<b>Number of Poles</b>	<b>SCCR</b>	<b>Max Horsepower Rating, 3-Ph</b>			<b>Wire Size</b>	<b>Wire Type</b>	<b>Part Number</b>
		30	CC	3	100kA	220/240Vac	440/480Vac	600 Vac	#14-10 Sol/Str	75°C Cu	RDF30CC-3
		30	CC	3 + Ntrl*	100kA	7.5	15	20	#14-10 Sol/Str	75°C Cu	RDF30CC-3N
		30	J	3	100kA	7.5	15	20	#14-10 Sol/Str	75°C Cu	RDF30J-3-COMP
		30	J	3 + Ntrl*	100kA	7.5	15	20	#14-10 Sol/Str	75°C Cu	RDF30J-3N-COMP
		* Neutral is switched.									
+											
HANDLE		<b>Direct Mount Handle - mounts directly to switch, no shaft required</b>									
		<b>For Switch Part Number</b>	<b>Color</b>	<b>Test Function</b>	<b>Padlockable</b>					<b>Part Number</b>	
		RDF30CC- RDF30J-_-COMP	Black Black	Y Y	Y Y					DIR-05 DIR-06	
OR											
SELECT FOR STANDARD APPLICATIONS		<b>External Front Operated Selector Handle - shaft required</b>									
		<b>NEMA Type</b>	<b>Color</b>	<b>Test Function</b>	<b>Padlockable</b>	<b>Defeatable</b>				<b>Part Number</b>	
		1, 3R, 4, 4X, 12	Black	N	Y	Y				H4X-04B	
		1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y				H4X-04R	
		<b>Shafts for Selector Handles</b>									
		<b>Length in (mm)</b>	<b>Mounting Depth (X) in (mm)</b>							<b>Part Number</b>	
		7.9 (200)	4.02~9.65 (102~245)							SH1-200	
		12.6 (320)	4.02~14.37 (102~365)							SH1-320	
		15.7 (400)	4.02~17.52 (102~445)							SH1-400	
OR											
HANDLE		<b>External Front Operated Pistol Handles - shaft required</b>									
		<b>NEMA Type</b>	<b>Color</b>	<b>Test Function</b>	<b>Padlockable</b>	<b>Defeatable</b>				<b>Part Number</b>	
		1, 3R, 12	Black	N	Y	Y				H12-05B	
		1, 3R, 12	Red/Yellow	N	Y	Y				H12-05R	
		1, 3R, 4, 4X, 12	Black	N	Y	Y				H4X-05B	
		1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y				H4X-05R	
		1, 3R, 4, 4X, 12	Black	Y	Y	Y				H4X-05TB	
		1, 3R, 4, 4X, 12	Red/Yellow	Y	Y	Y				H4X-05TR	
		<b>Metallic Hasp (Heavy Duty) External Front Operated Pistol Handles - shaft required</b>									
		<b>NEMA Type</b>	<b>Color</b>	<b>Test Function</b>	<b>Padlockable</b>	<b>Defeatable</b>				<b>Part Number</b>	
		1, 3R, 4, 4X, 12	Black	N	Y	Y				H4X-05BHD	
		1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y				H4X-05RHD	
		<b>Shafts for Pistol Handles</b>									
		<b>Length in (mm)</b>	<b>Mounting Depth (X) in (mm)</b>							<b>Part Number</b>	
		7.9 (200)	4.02~9.65 (102~245)							SH2-200	
		12.6 (320)	4.02~14.37 (102~365)							SH2-320	
		15.7 (400)	4.02~17.52 (102~445)							SH2-400	
OR											
ACCESSORIES		<b>NFPA Through the Door Handle Kit - to be used with selector handle or front pistol handle</b>									
		<b>Color</b>	<b>Test Function</b>	<b>Padlockable</b>	<b>Defeatable</b>					<b>Part Number</b>	
		Red	N	Y	N					H79-1	
and...											
ACCESSORIES		<b>Auxiliary Contacts</b>									
		<b>Contact Type</b>	<b>Number of Contacts</b>	<b>Continuous Amp Rating</b>	<b>Voltage Rating</b>	<b>Maximum Number of Auxiliary Contacts per Disconnect Switch Part Number</b>				<b>Part Number</b>	
		NO	1	10A	600Vac	RDF30CC-_: 4 / 8 with BAC-HOLDER2				BAC05 <sup>(1)</sup>	
		NC	1	10A	600Vac	RDF30J-_-COMP: 2 / 6 with BAC-HOLDER2				BAC06 <sup>(1)</sup>	
		Auxiliary Contact Holder				Accepts 4 Auxiliary Contacts: BAC05 or BAC06				BAC-HOLDER2 <sup>(2)</sup>	