

UL 98 Fused Rotary Disconnect Switches—600 & 800A

Standard Class J & Class L

For a Complete Assembly, Please Select:

Select for Standard Applications		Switch							
		Amp Rating	Fuse Class	Number of Poles	SCCR	Max Horsepower Rating, 3-Phase			Part Number
						220/240Vac	440/480Vac	600Vac	
		600	J	2	200kA	-	-	-	RDF600J-2
		600	J	3	200kA	200	400	500	RDF600J-3
		600	J	4	200kA	200	400	500	RDF600J-4
		800	L	2	200kA	-	-	-	RDF800L-2
		800	L	3	200kA	200	500	500	RDF800L-3
		800	L	4	200kA	200	500	500	RDF800L-4
		Terminal Lug Kit							
Switch Amp Rating	Number of Poles	Lugs Per Kit	Wire Range			Wire Type	Part Number		
600-800	2	2	(2) #2-600MCM			75°C Cu/Al	LUG5-2		
600-800	3	3	(2) #2-600MCM			75°C Cu/Al	LUG5-3		
600-800	4	4	(2) #2-600MCM			75°C Cu/Al	LUG5-4		
+									
Accessories		Direct Mount Handle - mounts directly to switch, no shaft required						Part Number	
		For Switch Part Number	Color	Test Function	Padlockable	Part Number			
		All Switches	Black	Y	Y	DIR-08			
		OR							
		External Front Operated Pistol Handles - shaft required						Part Number	
		NEMA Type	Color	Test Function	Padlockable	Defeatable	Part Number		
		1, 3R, 4, 4X, 12	Black	N	Y	Y	H4X-07B		
		1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y	H4X-07R		
		Metallic Hasp (Heavy Duty) External Front Operated Pistol Handles - shaft required						Part Number	
		NEMA Type	Color	Test Function	Padlockable	Defeatable	Part Number		
1, 3R, 4, 4X, 12	Black	N	Y	Y	H4X-07BHD				
1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y	H4X-07RHD				
Shafts for Pistol Handles						Part Number			
Length in (mm)	Mounting Depth (X) in (mm)								
7.9 (200)	10.63~11.97 (270~304)					SH7-200			
12.6 (320)	10.63~16.69 (270~424)					SH7-320			
15.7 (400)	10.63~19.84 (270~504)					SH7-400			
OR									
Accessories		NFPA Through the Door Handle Kit - to be used with front pistol handle						Part Number	
		For Switch Part Number	Color	Test Function	Padlockable	Defeatable	Part Number		
		All Switches	Red	N	Y	N	H79-4		
		and ...							
		Auxiliary Contacts						Part Number	
		Contact Type	Number of Contacts	Continuous Amp Rating	Voltage Rating	Max Number of Aux Contacts per Switch			
		NO	1	10A	600Vac	8		BAC05	
		NC	1	10A	600Vac	8		BAC06	
		and ...							
		Accessories		Terminal Shrouds - includes terminal shroud for lineside or loadside					Part Number
Switch Amp Rating	Number of Poles								
600-800	2						TSH10-2TB		
600-800	3						TSH10-3TB		
600-800	4						TSH10-4TB		