




Myers™ Hubs

Hub Basic Scru-Tite® – NEMA 2, 3, 3R, 4, 4X, and 12 Zinc

UL File No. E-27258








Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
ST 03†	3/8"	25	11
ST 1†	1/2"	25	19
ST 2†	3/4"	25	27
ST 3†	1"	25	40
ST 4†	1 1/4"	10	51
ST 5†	1 1/2"	10	68
ST 6†	2"	10	92
ST 7†	2 1/2"	5	210
ST 8†	3"	2	245
ST 9†	3 1/2"	2	278
ST 10†	4"	2	318
ST 11*	5"	1	478
ST 12*	6"	1	685

†Optional nickel-chrome plate finish. Add suffix -CP.
*Not supplied with insulator.

Hub Basic Scru-Tite® – NEMA 2, 3, 3R, 4, 4X, and 12 Aluminum

UL File No. E-27258








Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
STA 1	1/2"	25	8
STA 2	3/4"	25	11
STA 3	1"	25	17
STA 4	1 1/4"	10	30
STA 5	1 1/2"	10	30
STA 6	2"	10	38
STA 7	2 1/2"	5	80
STA 8	3"	2	100
STA 9	3 1/2"	2	138
STA 10	4"	2	150
STA 11*	5"	1	300
STA 12*	6"	1	300

*Not supplied with insulator.

Ground Hub – Stainless Steel Type 316 NEMA 2, 3, 3R, 4, 4X and 12

UL File No. E-59509

Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
SSTG 1	1/2"	10	29
SSTG 2	3/4"	10	41
SSTG 3	1"	10	57
SSTG 4	1 1/4"	5	73
SSTG 5	1 1/2"	5	99
SSTG 6	2"	5	134
SSTG 7	2 1/2"	2	183
SSTG 8	3"	2	278
SSTG 9	3 1/2"	2	328
SSTG 10	4"	2	395




Crouse-Hinds

by E.T.N

www.crouse-hinds.com US: 1-866-764-5454 CAN: 1-800-265-0502 Copyright© 2013 Eaton's Crouse-Hinds Business

Ground Hub – Zinc NEMA 2, 3, 3R, 4, 4X and 12

UL File No. E-59509




Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100	Max. Copper Grd. Wire Size	CSA‡	UL‡
STG 1	1/2"	25	20	#8	#8	#8
STG 2	3/4"	25	28	#8	#8	#8
STG 3	1"	25	42	#8	#8	#8
STG 4	1 1/4"	10	55	#8	#8	#8
STG 5	1 1/2"	10	70	#6	#8	#8
STG 6	2"	10	95	#4	#8	#8
STG 7	2 1/2"	5	190	#2	#6	#6
STG 8	3"	2	243	1 / 0	#6	#6
STG 9	3 1/2"	2	300	2 / 0	#6	#6
STG 10	4"	2	323	2 / 0	#4	#4
STG 11*	5"	1	625	2 / 0	#2	#2
STG 12*	6"	1	750	3 / 0	#1	#1

*Not supplied with insulator.

‡Use of wire terminal is required by CSA and recommended by UL for wire gauges over 10 AWG.

Ground Hub – Aluminum NEMA 2, 3, 3R, 4, 4X and 12

UL File No. E-59509

Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100	Max. Copper Grd. Wire Size	CSA‡	UL‡
STAG 1	1/2"	25	13	#8	#8	#8
STAG 2	3/4"	25	14	#8	#8	#8
STAG 3	1"	25	18	#8	#8	#8
STAG 4	1 1/4"	10	25	#8	#8	#8
STAG 5	1 1/2"	10	33	#6	#8	#8
STAG 6	2"	10	41	#4	#8	#8
STAG 7	2 1/2"	5	90	#2	#6	#6
STAG 8	3"	2	103	1 / 0	#6	#6
STAG 9	3 1/2"	2	138	2 / 0	#6	#6
STAG 10	4"	2	140	2 / 0	#4	#4
STAG 11*	5"	1	325	3 / 0	#2	#2
STAG 12*	6"	1	350	3 / 0	#1	#1

*Not supplied with insulator.

‡Use of wire terminal is required by CSA and recommended by UL for wire gauges over 10 AWG.

GP