











# Condulet® Conduit Bodies - Cast Iron or Aluminum

1F

Dimensions Pgs. See pages 10–12 (Dimensions for Form 5 – see Section CP)

## Threaded Rigid Bodies

| Shape   | Style     | Hub Size |        |        |         |         |         |         |         |         |         |  |
|---|-----------|----------|--------|--------|---------|---------|---------|---------|---------|---------|---------|--|
|   |           | 1/2      | 3/4    | 1      | 1 1/4   | 1 1/2   | 2       | 2 1/2   | 3       | 3 1/2   | 4       |  |
|                                  | <b>C</b>  |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | C17      | C27    | C37    | C47     | C57     | C67     | C77     | C87     |         |         |  |
|   | Form 8    | C18      | C28    | C38    | C448    | C58     | C68     | C78     | C88     |         |         |  |
|   | Mark 9    | C19      | C29    | C39    | C49     | C59     | C69     | C789    | C889    | C989    | C1089   |  |
|   | Form 5    | C50M     | C75M   | C100M  | C125M*  | C150M*  | C200M*  | C250M*  | C300M*  | C350M*  | C400M*  |  |
| Series 5  | C15       | C25      | C35    | C45    | C55     | C65     | C75     | C85     | C95*    | C105*   |         |  |
|                                  | <b>E</b>  |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | E17      | E27    | E37    |         |         |         |         |         |         |         |  |
|                                  | <b>L</b>  |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | L17      | L27    | L37    | L47     | L57     | L67     |         |         |         |         |  |
| Double faced – may be used as LL or LR – has 2 openings, one of which is furnished with a blank sheet steel cover |           |          |        |        |         |         |         |         |         |         |         |  |
|                                  | <b>LB</b> |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | LB17     | LB27   | LB37   | LB47    | LB57    | LB67    | LB777   | LB87    | LB97    | LB107   |  |
|   | Form 8    | LB18     | LB28   | LB38   | LB448   | LB58    | LB68    | LB78    | LB888   | LB98    | LB108   |  |
|   | Mark 9    | LB19     | LB29   | LB39   | LB49    | LB59    | LB69    | LB789   | LB889   | LB989   | LB1089  |  |
|   | Form 5    | LB50M    | LB75M  | LB100M | LB125M* | LB150M* | LB200M* | LB250M* | LB300M* | LB350M* | LB400M* |  |
| Series 5  | LB15      | LB25     | LB35   | LB45   | LB55    | LB65    | LB75    | LB85    | LB95    | LB105   |         |  |
|                                 | <b>LL</b> |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | LL17     | LL27   | LL37   | LL47    | LL57    | LL67    | LL777   | LL87    | LL97    | LL107   |  |
|   | Form 8    | LL18     | LL28   | LL38   | LL448   | LL58    | LL68    | LL78    | LL888   |         |         |  |
|   | Mark 9    | LL19     | LL29   | LL39   | LL49    | LL59    | LL69    | LL789   | LL889   | LL989   | LL1089  |  |
|   | Form 5    | LL50M    | LL75M  | LL100M | LL125M  | LL150M  | LL200M  | LL250M  | LL300M  | LL350M  | LL400M  |  |
| Series 5  | LL15      | LL25     | LL35   | LL45   | LL55    | LL65    | LL75    | LL85    | LL95    | LL105   |         |  |
|                                | <b>LR</b> |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | LR17     | LR27   | LR37   | LR47    | LR57    | LR67    | LR777   | LR87    | LR97    | LR107   |  |
|   | Form 8    | LR18     | LR28   | LR38   | LR448   | LR58    | LR68    | LR78    | LR888   |         |         |  |
|   | Mark 9    | LR19     | LR29   | LR39   | LR49    | LR59    | LR69    | LR789   | LR889   | LR989   | LR1089  |  |
|   | Form 5    | LR50M    | LR75M  | LR100M | LR125M  | LR150M  | LR200M  | LR250M  | LR300M  | LR350M  | LR400M  |  |
| Series 5  | LR15      | LR25     | LR35   | LR45   | LR55    | LR65    | LR75    | LR85    | LR95    | LR105   |         |  |
|                                | <b>T</b>  |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | T17      | T27    | T37    | T47     | T57     | T67     | T77     | T87     | T97     | T107    |  |
|   | Form 8    | T18      | T28    | T38    | T448    | T58     | T68     | T78     | T88     |         |         |  |
|   | Mark 9    | T19      | T29    | T39    | T49     | T59     | T69     | T789    | T889    | T989    | T1089   |  |
|   | Form 5    | T50M     | T75M   | T100M  | T125M   | T150M   | T200M   | T250M   | T300M   | T350M   | T400M   |  |
| Series 5  | T15       | T25      | T35    | T45    | T55     | T65     | T75     | T85     | T95*    | T105*   |         |  |
|                                | <b>TA</b> |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | TA17     | TA27   | TA37   | TA47    | TA57    | TA67    |         |         |         |         |  |
|                                | <b>TB</b> |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | TB17     | TB27   | TB37   | TB47    | TB57    | TB67    |         |         |         |         |  |
|   | Form 8    | TB18     | TB28   | TB38   | TB448   | TB58    | TB68    |         |         |         |         |  |
|   | Mark 9    | TB19     | TB29   | TB39   | TB49    | TB59    | TB69    |         |         |         |         |  |
|   | Form 5    | TB15     | TB25   | TB35   | TB45    | TB55    | TB65    |         |         |         |         |  |
| Series 5  | TB50M     | TB75M    | TB100M | TB125M | TB150M  | TB200M  |         |         |         |         |         |  |
|                                | <b>X</b>  |          |        |        |         |         |         |         |         |         |         |  |
|   | Form 7    | X17      | X27    | X37    | X47     | X57     | X67     |         |         |         |         |  |
|   | Form 8    | X18      | X28    | X38    | X448    | X58     | X68     |         |         |         |         |  |
|   | Mark 9    | X19      | X29    | X39    | X49     | X59     | X69     |         |         |         |         |  |
|   | Form 5    | X15      | X25    | X35    | X45     | X55     | X65     |         |         |         |         |  |
| Series 5  | X50M      | X75M     | X100M  | X125M  | X150M   | X200M   |         |         |         |         |         |  |

\* 1 1/4" - 4" Form 5 LB and C bodies are supplied with built-in rollers to facilitate wire pulling.

1F