

# Thin Wall Conduit Fittings (For EMT Conduit)

## Compression Type Fittings - Steel

### COMPRESSION TYPE FITTINGS – STEEL

#### Applications:

Thinwall conduit fittings are used:

- To join EMT to a box or enclosure
- To couple two ends of EMT conduit

#### Features:

- Compression Type
- Threadless
- Male Hub Threads - NPSM
- Steel Locknuts
- Heavy Steel Walls
- Standard Material: Steel
- Standard Finish: Zinc Plated

### Concrete Tight Straight Connectors – Insulated

UL File No. E-22132



| Cat. # | Size   | Unit Qty. | Wt. Lbs. Per 100 |
|--------|--------|-----------|------------------|
| 1650   | 1/2"   | 50        | 11               |
| 1651   | 3/4"   | 25        | 16               |
| 1652   | 1"     | 25        | 25               |
| 1653   | 1 1/4" | 10        | 43               |
| 1654   | 1 1/2" | 10        | 54               |
| 1655   | 2"     | 5         | 76               |
| 1656   | 2 1/2" | 2         | 190              |
| 1657   | 3"     | 1         | 300              |
| 1658   | 3 1/2" | 1         | 330              |
| 1659   | 4"     | 1         | 360              |

### Straight Connectors – Non-Insulated

UL File No. E-22132



| Cat. # | Size   | Unit Qty. | Wt. Lbs. Per 100 |
|--------|--------|-----------|------------------|
| 650S   | 1/2"   | 50        | 9                |
| 651S   | 3/4"   | 25        | 16               |
| 652    | 1"     | 25        | 25               |
| 653    | 1 1/4" | 10        | 43               |
| 654    | 1 1/2" | 10        | 54               |
| 655    | 2"     | 5         | 76               |
| 656    | 2 1/2" | 2         | 190              |
| 657    | 3"     | 1         | 300              |
| 658    | 3 1/2" | 1         | 280              |
| 659    | 4"     | 1         | 360              |

### Couplings

UL File No. E-22132



| Cat. # | Size   | Unit Qty. | Wt. Lbs. Per 100 |
|--------|--------|-----------|------------------|
| 660S   | 1/2"   | 50        | 12               |
| 661S   | 3/4"   | 25        | 18               |
| 662    | 1"     | 25        | 27               |
| 663    | 1 1/4" | 10        | 46               |
| 664    | 1 1/2" | 10        | 63               |
| 665    | 2"     | 5         | 92               |
| 666    | 2 1/2" | 2         | 250              |
| 667    | 3"     | 1         | 410              |
| 668    | 3 1/2" | 1         | 390              |
| 669    | 4"     | 1         | 485              |

GP