

# PRE-formance™ Basic Assemblies

Cat. #	Description	Capacity Cu. In.	Unit Qty.	Wt. Lbs. Per 100
<b>Pre-Fabricated Box, Cover, Ground Screw and Lead Assembly</b>				
<b>For AC/MC Cable</b>				
TP30454PF	1 1/2" Deep Welded Box assembled to 1/2" Raised Single Gang Uni-Mount Cover	24.8	25	114
TP31454PF	1 1/2" Deep Welded Box assembled to 5/8" Raised Single Gang Uni-Mount Cover	25.3	25	117
TP32454PF	1 1/2" Deep Welded Box assembled to 3/4" Raised Single Gang Uni-Mount Cover	26.5	25	121
TP35454PF	1 1/2" Deep Welded Box assembled to 1/2" Raised Two Gang Uni-Mount Cover	27.0	25	109
TP36454PF	1 1/2" Deep Welded Box assembled to 5/8" Raised Two Gang Uni-Mount Cover	29.0	25	123
TP37454PF	1 1/2" Deep Welded Box assembled to 3/4" Raised Two Gang Uni-Mount Cover	30.0	25	125
TP30431PF	2 1/8" Deep Welded Box assembled to 1/2" Raised Single Gang Uni-Mount Cover	34.1	25	134
TP31431PF	2 1/8" Deep Welded Box assembled to 5/8" Raised Single Gang Uni-Mount Cover	34.6	25	137
TP32431PF	2 1/8" Deep Welded Box assembled to 3/4" Raised Single Gang Uni-Mount Cover	35.8	25	141
TP35431PF	2 1/8" Deep Welded Box assembled to 1/2" Raised Two Gang Uni-Mount Cover	36.3	25	129
TP36431PF	2 1/8" Deep Welded Box assembled to 5/8" Raised Two Gang Uni-Mount Cover	38.3	25	143
TP37431PF	2 1/8" Deep Welded Box assembled to 3/4" Raised Two Gang Uni-Mount Cover	39.3	25	145



**Open Back Box**

Innovative Open Back Boxes maximize working area to reduce wiring time and eliminate interference problems. Eliminates the need for disassembly at the job site. All open back box assemblies are shipped with TP472 flat, blank back covers.

Cat. #	Description	Capacity Cu. In.	Unit Qty.	Wt. Lbs. Per 100
<b>Pre-Fabricated Open Back Box, Cover, Ground Screw and Lead Assembly</b>				
<b>For Conduit</b>				
TP3040DPF	2 1/8" Deep Welded Open Back Box, 1/2" Raised Single Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	107
TP3140DPF	2 1/8" Deep Welded Open Back Box, 5/8" Raised Single Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	110
TP3240DPF	2 1/8" Deep Welded Open Back Box, 3/4" Raised Single Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	114
TP3540DPF	2 1/8" Deep Welded Open Back Box, 1/2" Raised Two Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	112
TP3640DPF	2 1/8" Deep Welded Open Back Box, 5/8" Raised Two Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	116
TP3740DPF	2 1/8" Deep Welded Open Back Box, 3/4" Raised Two Gang Uni-Mount Cover, ground screw, lead, and back cover	34.1	25	118

Additional Uni-Mount / box configurations available. Consult factory for details.  
Remove the PF for boxes without ground screw and lead.  
For stranded wire replace PF with PFA