

Cam-Lok® “J” Power Series

E1016 Series



E1016-1602S



E1016-1600

All Cam-Lok part numbers available in convenient, single-use, color-coded packaging.

INSULATED RECEPTACLES - THREADED PANEL MOUNTS			
	COLOR	MALE COMPLETE PART NO.	FEMALE COMPLETE PART NO.
1 1/8" THREADED STUD	BLACK	E1016-1600S	E1016-1631S
	RED	E1016-1602S	E1016-1633S
	GREEN	E1016-1604S	E1016-1635S
	WHITE	E1016-1605S	E1016-1636S
	BLUE	E1016-1612S	E1016-1643S
	BROWN	E1016-1619S	E1016-1687S
	ORANGE	E1016-1603S	E1016-1634S
	YELLOW	E1016-1601S	E1016-1632S

Stud size 1/2"-13, maximum torque 40 ft. lbs.

INSULATED RECEPTACLES			
	COLOR	MALE COMPLETE PART NO.	FEMALE COMPLETE PART NO.
3/4" THREADED STUD	BLACK	E1016-1600	E1016-1631
	RED	E1016-1602	E1016-1633
	GREEN	E1016-1604	E1016-1635
	WHITE	E1016-1605	E1016-1636
	BLUE	E1016-1612	E1016-1643
	BROWN	E1016-1619	E1016-1687
	ORANGE	E1016-1603	E1016-1634
	YELLOW	E1016-1601	E1016-1632

Stud size 1/2"-13, maximum torque 40 ft. lbs.

CAM-LOK “J” POWER SERIES
RECEPTACLES AND PLUGS PROVIDE THE MEANS TO QUICKLY CONNECT AND DISCONNECT POWER SYSTEMS SAFELY AT CONCERTS AND CARNIVALS AS WELL AS CONNECTING GENERATORS, STANDBY POWER, AND LOAD TESTING IN HOSPITALS, UTILITIES AND HEAVY INDUSTRIAL ENVIRONMENTS.

RATINGS: 600 VOLTS UP TO 250 AMPERES CONTINUOUS

STANDARD MATERIALS
CABLE SIZE: #6-250 MCM
RECEPTACLE BODY: TPE
CONTACT: BRASS

AGENCY APPROVALS
UL LISTED E67181
CSA CERTIFIED LR13963

ENVIRONMENTAL RATING: NEMA 3R

