

# Rigid/Intermediate Grade Conduit Fittings

## Push Plugs, Snap-In Blanks, Reducing Washers

### PUSH PLUGS – PLASTIC\*



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
PPC 50	1/2"	100	1
PPC 75	3/4"	100	1
PPC 100	1"	50	1
PPC 125	1 1/4"	50	1
PPC 150	1 1/2"	25	1
PPC 200	2"	25	1
PPC 250	2 1/2"	100	2
PPC 300	3"	100	3
PPC 350	3 1/2"	50	6
PPC 400	4"	50	8

\*Temperature Rating: 180° – 200°F  
Tensile Strength: 600 – 2300 PSI

### KNOCKOUT REDUCING WASHERS – STEEL



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
342	3/4" – 1/2"	100	1
343	1" – 1/2"	100	2
344	1" – 3/4"	100	2
345	1 1/4" – 1/2"	100	3
346	1 1/4" – 3/4"	100	2
347	1 1/4" – 1"	100	2
348	1 1/2" – 1/2"	50	5
349	1 1/2" – 3/4"	50	4
350S	1 1/2" – 1"	50	4
351	1 1/2" – 1 1/4"	50	3
352	2" – 1/2"	50	7
353	2" – 3/4"	50	7
354	2" – 1"	50	6
355	2" – 1 1/4"	50	5
356	2" – 1 1/2"	50	3
360	2 1/2" – 1/2"	25	7
361	2 1/2" – 3/4"	25	7
362	2 1/2" – 1"	25	7
363	2 1/2" – 1 1/4"	25	7
364	2 1/2" – 1 1/2"	25	7
365	2 1/2" – 2"	25	7
366	3" – 1"	25	14
367	3" – 1 1/4"	25	14
368	3" – 1 1/2"	25	14
369	3" – 2"	25	14
370 S	3" – 2 1/2"	25	14
371	3 1/2" – 1 1/2"	25	25
372	3 1/2" – 2"	25	25
373	3 1/2" – 2 1/2"	25	25
374	3 1/2" – 3"	25	25
375	4" – 2"	25	35
376	4" – 2 1/2"	25	35
377	4" – 3"	25	35
378	4" – 3 1/2"	25	35

### KNOCKOUT SNAP-IN BLANKS – STEEL



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
335	1/2"	100	2
336	3/4"	100	2
337	1"	50	2
338	1 1/4"	50	3
339	1 1/2"	50	5
340	2"	20	7

### CONCRETE SLAB INSERTS - 90 DEGREE

#### Application:

- For use with Rigid and IMC
- For conduit installed in poured concrete slabs
- 90 Degree design eliminates the need to bend conduit
- Provides flush threaded conduit hub for connecting Rigid and IMC conduit and allows future access to conduit system
- Used in in-slab ceiling & floor poured applications

#### Standard Materials:

- Zinc Die Cast



Cat. #	EMT	Unit Qty.	Wt. Lbs. Per 100
ESL75	3/4"	5	41
ESL100	1"	5	57

#### Dimensions

##### In Inches:

Cat. #	A	B	C	D	E	F	G
ESL75	4.55	3.72	3.49	3.15	2.13	1.14	0.20
ESL100	4.68	3.84	3.46	3.10	2.44	1.47	0.19

