

# Rigid/Intermediate Grade Conduit Fittings

## Conduit Clamps, Straps, Hangers

### CABLE AND CONDUIT HANGERS – STEEL

#### Certifications and Compliances:

- UL Listed

#### With Bolt



Cat. #	Conduit Size EMT	Conduit Sizes Rigid	Unit Qty.	Wt. Lbs. Per 100
0B	1/2"	3/8" & 1/2"	100	6
1B	3/4"	3/4"	100	6
2B	1"	1"	100	8
2 1/2 B	1 1/4"	—	100	10
3B	1 1/2"	1 1/4"	100	11
4B	—	1 1/2"	100	16
5B	2"	2"	50	23
6B	2 1/2"	2 1/2"	50	29
7B	3"	3"	25	31
8B	3 1/2"	3 1/2"	10	38
9B	4"	4"	10	38

### CABLE AND CONDUIT HANGERS - STEEL

#### Applications:

- Used to provide mechanical support to conduit and raceway systems

#### Certifications and Compliances:

- UL Listed
- cUL Listed

#### With Extruded Hole and Bolt



Cat. #	Description	Unit Qty.	Wt. Lbs. Per 100
0BX	3/8 AND 1/2 RGD 1/2 EMT	100	6
1BX	3/4 RGD 3/4 EMT	100	7
2BX	1 RGD 1 EMT	100	11
2 1/2BX	1 1/4 EMT	100	10
3BX	1 1/4 RGD 1 1/2 EMT	100	13
4BX	1 1/2 RGD	100	16
5BX	2 RGD 2 EMT	50	17

### BEAM CLAMPS/INSULATOR SUPPORTS – MALLEABLE IRON

#### Standard Finishes:

- Zinc Plated

UL File No. E-184283



Cat. #	Base Size	Jaw Open	Max. Wt. Support	Tapped Holes	Unit Qty.	Wt. Lbs. Per 100
528	3/4"	5/8"	50	10 – 24	25	14
529	3/4"	5/8"	50	1/4" – 20	25	13
530	1"	3/4"	60	10 – 24	25	23
531	1"	3/4"	60	1/4" – 20	25	24
532	1 1/2"	3/4"	80	3/16" – 18	50	47
533	2"	7/8"	100	3/8" – 16	25	81
534	2 1/2"	7/8"	200	1/2" – 13	25	155

### BEAM CLAMPS/INSULATOR SUPPORTS – STEEL



Cat. #	Base Size	Jaw Opening	Tapped Holes	Unit Qty.	Wt. Lbs. Per 100
529 S	3/4"	5/8"	1/4" – 20	50	13

### CONDUIT CLAMPS - RIGHT ANGLE TYPE - MALLEABLE IRON

#### Applications:

- Right Angle – to attach the conduit run at a 90° angle to a beam or structural member
- Paralled Type – to attach the conduit run parallel to a beam or structural member



Cat. #	Trade Size	Load Rating Lbs.	Wt. Lbs. Per 100
RAC50HD	1/2"	30	37
RAC75HD	3/4"	50	40
RAC100HD	1"	60	42
RAC125HD	1 1/4"	75	49
RAC150HD	1 1/2"	80	54
RAC200HD	2"	100	71
RAC250HD	2 1/2"	125	95
RAC300HD	3"	165	107
RAC350HD	3 1/2"	200	120
RAC400HD	4"	330	131