

RPC Circuit Breaking Power Connectors With Solder Well Terminals†



Cable Diameter Range	Cord Connector Cat. #§	Plug Cat. #§
.250 to .625 .625 to .875	RPC317 160 S09A RPC317 161 S09A	RPC117 150 P09A RPC117 151 P09A
.250 to .625 .625 to .875	RPC317 160 S08N RPC317 161 S08N	RPC117 150 P08N RPC117 151 P08N
.250 to .625 .625 to .875	RPC317 160 S02A RPC317 161 S02A	RPC117 150 P02A RPC117 151 P02A
.250 to .625 .625 to .875	RPC317 160 S04A RPC317 161 S04A	RPC117 150 P04A RPC117 151 P04A
.625 to 1.000 1.000 to 1.187	RPC321 161 S17A RPC321 395 S17A	RPC121 151 P17A RPC121 387 P17A
.250 to .625 .625 to .875	RPC317 160 S01N RPC317 161 S01N	RPC117 150 P01N RPC117 151 P01N
.250 to .625 .625 to .875	RPC317 160 S03N RPC317 161 S03N	RPC117 150 P03N RPC117 151 P03N
.625 to 1.000 1.000 to 1.187	RPC321 161 S16N RPC321 395 S16N	RPC121 151 P16N RPC121 387 P16N
.875 to 1.375 1.375 to 1.625 1.625 to 1.875	RPC333 163 S08A RPC333 396 S08A RPC333 397 S08A	RPC133 153 P08A RPC133 388 P08A RPC133 389 P08A
.875 to 1.375 1.375 to 1.625 1.625 to 1.875	RPC333 163 S09A RPC333 396 S09A RPC333 397 S09A	RPC133 153 P09A RPC133 388 P09A RPC133 389 P09A
.875 to 1.375 1.375 to 1.625 1.625 to 1.875	RPC333 163 S05N RPC333 396 S05N RPC333 397 S05N	RPC133 153 P05N RPC133 388 P05N RPC133 389 P05N
.875 to 1.375 1.375 to 1.625 1.625 to 1.875	RPC333 163 S06N RPC333 396 S06N RPC333 397 S06N	RPC133 153 P06N RPC133 388 P06N RPC133 389 P06N

†Solder well terminals provided as standard. Crimp contacts are optionally available, add suffix T to catalog number. Example: RPC217-014-S09AT-ARE23.
‡For square flanged receptacle *without* dust cap, change the middle three digits of the catalog number from 014 to 127. Example: RPC217-127-S09A-ARE23.
*For square flanged receptacle with dust cap for panel mounting, delete the last digits of the catalog number specifying the backbox. Example: RPC217-014-S09A.
§For plugs and cord connectors:
Liquidtight/Conduit Adapter –
To order with adapter, add letters "LT" to first section of catalog number. Example: RPCLT317-160-S09A.
Additional Cable Strain Relief Options –
• Stainless steel wire mesh grip – To order, add letter "K" to first section of catalog number. Example: RPCK317-160-S09A.

Note: RPC with pressure terminals are also available, see pages 1438–1441.

