



Other options and accessories available. Consult website: [www.cooperlighting.com](http://www.cooperlighting.com).

## PD6V142 6" Vertical Downlight

Accepts (1) 26 DTT or 26/32/42W TTT lamp

- Boat-shaped galvanized steel frame with a preset 1/2" plaster lip that adjusts to accommodate ceilings up to 2" thick.
- May be used for new construction or remodeling installations.
- Pre-installed and pre-centered No Fuss Bar Hangers™, or use with 1/2" EMT.
- Bar hanger receivers adjust 2" vertically from above the ceiling or through the aperture.
- Reflector assembly is retained with two torsion springs and held tightly to the finished ceiling surface.
- (4) 1/2" and (2) 3/4" trade size pry outs positioned to allow straight conduit runs. Listed for feed through branch wiring.
- 4-pin G24q base accepts (1) 26W DTT or 26/32/42W TTT lamp.
- Universal 120V - 277V UNV electronic ballast for 26/32/42W compact fluorescent lamp.
- Optional 120V/277V CFL battery pack provides 90 minutes of emergency illumination. (REM option - see product overview page.)

### SAMPLE NUMBER: PD6V142E 60VC

Order housing, reflector and lamp separately for a complete luminaire.

Housing	Ballast Option	Reflector	Finish Option	Flange Option
PD6V142 = 6 Inch vertical (1) 26/32/42W DTT/TTT CFL	<b>REM</b> = 120V/277V 60Hz dual-tap emergency battery ballast with remote test switch plate <b>1DMARKX</b> = 5% two-wire (26/32/42W) dimming, 120V <b>2DMARKX</b> = 5% two-wire (26/32/42W) dimming, 277V	60V = 6" vertical	C=Specular Clear H=Specular Clear	Blank=Polished Flange WF=White Paint Flange

### SAMPLE NUMBER: PD6V142E 60VWWC

Order housing, reflector and lamp separately for a complete luminaire.

Housing	Ballast Option	Reflector	Finish Option	Flange Option
PD6V142 = 6 Inch vertical (1) 26/32/42W DTT/TTT CFL	<b>E</b> = 120 - 277V 50/60Hz UNV <b>REM</b> = 120V/277V 60Hz dual-tap emergency battery ballast with remote test switch plate <b>1DMARKX</b> = 5% two-wire (26/32/42W) dimming, 120V <b>2DMARKX</b> = 5% two-wire (26/32/42W) dimming, 277V	60VWW = 6" vertical open wall wash	C=Specular Clear H=Specular Clear	Blank=Polished Flange WF=White Paint Flange

### SAMPLE NUMBER: PD6V142E 60VW

Order housing, reflector and lamp separately for a complete luminaire.

Housing	Ballast Option	Reflector	Regressed Lens	Flange Option
PD6V142 = 6 Inch vertical (1) 26W DTT, 26/32/42W DTT/TTT CFL	<b>E</b> = 120 - 277V 50/60Hz UNV <b>REM</b> = 120V/277V 60Hz dual-tap emergency battery ballast with remote test switch plate <b>1DMARKX</b> = 5% two-wire (26/32/42W) dimming, 120V <b>2DMARKX</b> = 5% two-wire (26/32/42W) dimming, 277V	60V = 6" vertical	1G=Prismatic Glass	Blank=Polished Flange WF=White Paint Flange

## Ordering Information

Catalog Number	Description	UPC Code	Weight	Case Qty	Pallet Qty
<b>Vertical 6" Compact Fluorescent</b>					
PD6V142E	Housing, 6" (1) 26W DTT, 26/32/42W TTT Vertical, 120V-277V UNV	080083611812	4	6	48
PD6V142REM	Housing, 6" (1) 26W DTT, 26/32/42W TTT Vertical, 120V/277V Emergency	080083611713	9	1	18
PD6V1421DMARKX	Housing, 6" (1) 26W DTT, 26/32/42W TTT Vertical, 120V Dimming	080083652792	4	6	48
PD6V1422DMARKX	Housing, 6" (1) 26W DTT, 26/32/42W TTT Vertical, 277V Dimming	080083649754	4	6	48
60VC	Reflector, 6" Vertical, Open Reflector, Specular Clear	080083605286	1.43	1	125
60VWWC	Reflector, 6" Vertical, Open Wall Wash, Specular Clear	080083605293	1.43	1	125
60V1GC	Reflector, 6" Vertical, Lens, Prismatic Glass Specular Clear	080083652969	1.71	1	125
60V1GCWF	Reflector, 6" Vertical, Lens, Prismatic Glass Specular Clear, White Flange	080083652754	1.71	1	125
60V1GH	Reflector, 6" Vertical, Lens, Prismatic Glass Semi Specular Clear	080083652884	1.71	1	125
60V1GHWF	Reflector, 6" Vertical, Lens, Prismatic Glass Semi Specular Clear, White Flange	080083652747	1.71	1	125
60VCWF	Reflector, 6" Vertical, Open Reflector, Specular Clear, White Flange	080083652730	1.43	1	125
60VH	Reflector, 6" Vertical, Open Reflector, Semi Specular Clear	080083652891	1.43	1	125
60VHWF	Reflector, 6" Vertical, Open Reflector, Semi Specular Clear, White Flange	080083652723	1.43	1	125
60VWWCWF	Reflector, 6" Vertical, Open Wall Wash Specular Clear, White Flange	080083652716	1.43	1	125
60VWWH	Reflector, 6" Vertical, Open Wall Wash Semi Specular Clear	080083652860	1.43	1	125
60VWWHWF	Reflector, 6" Vertical, Open Wall Wash Semi Specular Clear, White Flange	080083652709	1.43	1	125
60V1GW	Reflector, 6" Vertical, Lens, Prismatic Glass Gloss White	080083652877	1.71	1	125

## Accessories

Accessories	Description	UPC Code	Weight	Case Qty	Pallet Qty
RMB22	Optional bar hangers (pair) with integral nail for frame construction	662401000821	1	4	756