



Actual

Catalog Number: ADR11-34
Product ID: 7TAH006600R0196
UPC Number: 78378661007
Status: Active

Type ADR-ALCUL Three-Conductor, Four-Hole Mount for Conductor Range Max 1/0 Str, Min 14 AWG, 3/8 Inch Bolt Hole, NEMA Spacing 1-3/4 Inch Centers, Length 2-29/32 Inch, Tin Plated

- Easy Installation - no special tools required.

North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Dual-Rated Mechanical Connector
Special Features	Easy Installation - no special tools required.
Standard	UL E9809
Number Of Conductors	3
Material	Aluminum
Finish	Tin-Plated
Conductor Range (Main/Primary)	14-1/0
Number Of Mounting Holes	4
Mounting Hole Spacing	3/8 Inch

Packaging

Inner Quantity	6
Inner Dimensions (inches)	3.4x3.5x3.9
Outer Quantity	60
Outer Dimensions (inches)	10x7x7.9
Weight Uom	18.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com