



Representative

Catalog Number: AL44
Product ID: 7TAA268500R0016
UPC Number: 78378604735
Status: Active

Aluminum Two-Hole Lug - Straight Long Barrel, Wire Range 636 26/7, 715 54/7, 666 24/7 ASCR, 750-800 Stranded, 1/2 Inch Bolt Size, Blind-End, Hydraulic Dies: 1 1/2, 6024AH, 125H, 301, CSA 30

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Compression Connector
Special Features	PreFilled with Compound. Complete Die and Crimp information clearly indented on each lug. Installed with standard tools and dies. Use 1/2 inch mounting hardware for all sizes.
Application	For Aluminum and Copper Conductor.
Cable Size	636 26/7, 715 54/7, 666 24/7 ASCR, 750-800 Stranded
Number Of Holes	2
Material	Aluminum
Mounting	NEMA Standard Mounting Holes
Connection	Crimp

European Specifications (ETIM)

ETIM	EC001053 Crimp cable lug for aluminium conductors
Material	Aluminium
Number of fixing holes	2
Sleeve form	Long

Packaging

Outer Quantity	20
Outer Dimensions (inches)	12.8x11.9x6.1
Weight Uom	102.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com