



Representative

**Catalog Number:** CSP400  
**Product ID:** 7TAH007500R0040  
**UPC Number:** 78378613215  
**Status:** Active

Type CSP Copper Splice, Short Barrel, Max 35kV, Wire Size 400 kcmil, Tin Plated, Die Color Code Blue

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Short Barrel Copper Splice
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Conductor Range	400 kcmil
Material	Copper
Finish	Tin Plated
Color	Blue
Voltage Rating	35KV

### Packaging

Inner Quantity	6
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	60
Outer Dimensions (inches)	3.6x3.3x3.3
Weight Uom	20 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)