



Actual

Catalog Number: JB12B
Product ID: 7TAA131990R0258
UPC Number: 78378685100
EAN Number: 05415022359527
Status: Obsolete
Replacement Catalog: TBM14M

12 Ton Manual Hydraulic Crimp Tool with Carrying Case - 180 Degree Head Rotation, Accepts All U-Type Dies

North American Specifications (UNSPSC)

UNSPSC	27111518 Wire lug crimping tool
IGCC	1967 Wire lug crimping tool
Brand Name	Blackburn
Type	Manual and Power-Assisted Compression Tools
Application	Up to 750 kcmil copper lugs & splices, Up to 650 kcmil aluminum lugs & splices, CHT814-10 to CHT2502-6 copper H-Taps, 63105 to 63148 aluminum H-Taps, 54755 to 54770 C-Taps
Overall Length	22.75 Inches

Packaging

Outer Quantity	1
Outer Dimensions (inches)	30.25x9.5x6.5
Weight Uom	1900 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com