

DESCRIPTION

The Lumark LMQF/LTMQ is ideal for small yards, walkways, entrances and decks, as well as for accent lighting. U.L. listed and CSA certified for wet locations. For outdoor use only.

SPECIFICATION FEATURES

- Corrosion-resistant die-cast aluminum construction for long life
- Durable die-cast aluminum mounting plate on LTMQ. LMQF supplied with adjustable knuckle to fit 1/2" NPS connection. Ideal for wall or eave mounted applications
- Tempered safety glass lens
- 150W Quartz Halogen lamps included
- Durable polyester powder coat finish. Available in bronze or white



LTMQ LMQF DECORATIVE HALOGEN FLOOD

1 5 0 W
Quartz Halogen

DECORATIVE
HALOGEN FLOOD

Catalog Number	Lamp Type/Base	Lamp Wattage	Voltage	Color	Net Wt. (lbs.)
LMQF150	Quartz Halogen	150	120V	Bronze	1.23
LMQF150W	Quartz Halogen	150	120V	White	1.23
LTMQ150	Quartz Halogen	(2) 150	120V	Bronze	2.71
LTMQ150W	Quartz Halogen	(2) 150	120V	White	2.71

DESCRIPTION

The Lumark LMT250 is ideal security lighting for many commercial or residential application. U.L. and cUL listed for wet locations.

SPECIFICATION FEATURES

- Toolless adjustable die-cast lamp holders
- 150W Maximum PAR 38 incandescent lamps. Lamps not included
- Die-cast aluminum weatherproof housing
- Universal die-cast mounting plate for wall or eave mount. Hardware and gasket included
- Durable polyester powder coat in bronze or optional white



LMT FLOODLIGHT

(2) 1 5 0 W
M A X I M U M
I N C A N D E S C E N T

FLOODLIGHT

Catalog Number	Lamp Type	Max. Lamp Wattage	Voltage	Color	Net Wt. (lbs.)
LMT125	Incandescent	(1) 150W	120V	Bronze	0.67
LMT125W	Incandescent	(1) 150W	120V	White	0.67
LMT250	Incandescent	(2) 150W	120V	Bronze	1.05
LMT250W	Incandescent	(2) 150W	120V	White	1.05