



Representative

Catalog Number: C2-BB
Product ID: 7TAA267160R0001
UPC Number: 78378633100
EAN Number: 05414363149057
Status: Active

Insulating Polypropylene Cover for All 5/8 inch O.D., sleeves 2 inch long or less

North American Specifications (UNSPSC)

UNSPSC	39121468 Input output connector cover
IGCC	4698 Input output connector cover
Brand Name	Blackburn
Type	Type C, H-Type Compression Connector Cover
Special Features	Thin Strips of the Grass-Skirt mold around the conductors to provide a highly reliable end enclosure. Tapered Drains in both cover halves prevent accumulation of water within the cover, regardless of which half of the cover is down. Made from Black Polypropylene to resist the elements, UV sun rays and common contaminants.
Application	Secure Double-Locking latches, provide a close-fitting top and bottom seal.
Material	Polypropylene
Color	Black
Mounting	None
Length	4.00 inches
Width	1.05 inches
Height	1.10 inches

Packaging

Inner Quantity	100
Outer Quantity	400
Outer Dimensions (inches)	13.9x13.3x13.3
Weight Uom	2.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com