



Canopy Switches

Canopy Switches

Features:

- Meets all UL 20 requirements.
- Wide variety of sizes for use in fixtures, appliances, and equipment.
- Shank is threaded 15/32" - 32 x 15/32" long.
- Hex nut and finishing nut furnished.
- 6 wire lead terminals, #18 105°C stripped 3/4".



459



449



458

Turn Knob - Metal

Catalog No.

Rating	Circuit	Sequence	Finish	
3A 125V "T"; 1A 250V	Two Circuit	LO-MED-HI-OFF	Nickel	488NP
			Brass	488BD
3A 125V; 1A 125V "T"; 1A 250V	Single Pole	ON-OFF	Nickel	443NP
			Brass	443BD

Turn Knob - Plastic

Catalog No.

Rating	Circuit	Sequence	Finish	
3A 125V; 1A 125V "T"; 1A 250V	Single Pole	ON-OFF	Brown	459

Push Button - Metal

Catalog No.

Rating	Circuit	Sequence	Finish	
3A 125V; 1A 125V "T"; 1A 250V	Single Pole	ON-OFF	Nickel	449NP
			Brass	449BD

Push Button - Plastic

Catalog No.

Rating	Circuit	Sequence	Finish	
3A 125V; 1A 125V "T"; 1A 250V	Single Pole	ON-OFF	Brown	466
8A 120V AC	Single Pole	ON-OFF	Brown	435

Pull Chain - End Bell

Catalog No.

Rating	Circuit	Sequence	Finish	
6A 125V AC; 3A 125V "T"; 3A 250V AC	Single Pole	ON-OFF	Nickel	442
			Brass	460
6A 125V; 3A 250V	Two Circuit	LO-MED-HI-OFF	Brass	460
1A 250V; 3A 125V; 1A 125V "T"	Single Pole	ON-OFF	Nickel	458NP
			Brass	458BD



B14

Switches