



Powering Business Worldwide

7503-9A

SWITCH DECOR. 3W 15A 120/277V AG AL

UPC: 032664737336

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Duplex, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: Ivory
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth X 4.19 In Height
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)

7503-9B

SWITCH DECOR. 3W 15A 120/277V AG BR

UPC: 032664737343

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Duplex, Decorator, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: White
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 1.32 In Width X 0.82 In Depth X 4.19 In Height
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

7503-9BK

SWITCH DECOR. 3W 15A 120/277V AG BK

UPC: 032664737350

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Decorator, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade dec
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 250 V
Material: Nylon Face, PVC Base
Color: White
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 0.88 X 1.32 X 3.28X 4.19 IN
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Nylon Face
Temperature Rating: -20C to 70C (-4F to 158F)

7503-9GY

SWITCH DECOR. 3W 15A 120/277V AG GY

UPC: 032664737367

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Duplex, Straight Blade
Special Features: Wiring Type Back and Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: Nylon Face, PVC Base
Color: Ivory
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 0.88 In Depth X 4.19 In Height
Environmental Conditions: Indoor
Dielectric Strength: 2000 V
Insulation: Nylon Face, PVC Base
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

7503-9LA

SWITCH DECOR. 3W 15A 120/277V AG LA

UPC: 032664737374

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Duplex, Straight Blade
Special Features: Wiring Type Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 10 AWG
Amperage Rating: 20 Amp
Voltage Rating: 125 Vac
Material: PVC
Color: Black
NEMA Rating: 5-20R
Mounting: Flush
Connection: Screw
Size: 0.82 In Depth X 4.19 In Height
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: PVC
Temperature Rating: -20C to 70C (-4F to 158F)

7503-9V

SWITCH DECOR. 3W 15A 120/277V AG IV

UPC: 032664737381

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single Locking
Special Features: Wiring Type Back Wire
Application: Comm l grd recpts
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 0
Amperage Rating: 20 Amp
Voltage Rating: 250v
Material: Rugged Nylon
Color: Black
NEMA Rating: L6-20
Mounting: Flush
Connection: Screw
Size: 1.70 In Width X 1.15 In Depth
Environmental Conditions: See Spec Sheet
Dielectric Strength: 250 Vac
Insulation: Nylon
Temperature Rating: 0



Powering Business Worldwide

7503-9W

SWITCH DECOR. 3W 15A 120/277V AG WH

UPC: 032664737398

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features:

Application: Commercial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 4 AWG

Amperage Rating: 30 Amp

Voltage Rating: 125 Vac

Material: High Strength Glass Reinforced Nylon

Color: Black

NEMA Rating: TT-30R

Mounting: Panel

Connection: Screw

Size: 2.09 In Diameter X 1.69 In Height

7503A

Switch Decorator 3Way 15A 120/277V AL

UPC: 032664627637

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features: Flush

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 4 AWG

Amperage Rating: 50 Amp

Voltage Rating: 250Vac

Material: Receptacles

Color: Black

NEMA Rating: 6-50R

Mounting: Flush

Connection: Plug

Size: 2.10X2.40X4.75In

Environmental Conditions: Indoor

Dielectric Strength: 250 Vac

Insulation: Receptacles

Temperature Rating: INDOOR



Powering Business Worldwide

7503A-C

Switch Deco 3Way 15A 120/277V AL Can

UPC: 032664643477

7503B-BOX

Switch Decorator 3Way 15A 120/277V BR

UPC: 032664627804

7503BK-BOX

Switch Decorator 3Way 15A 120/277V BK

UPC: 032664627866

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Standard Grade, High Impact Resistant, Wiring Type Push

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Black

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 1.31 In Width X 0.69 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 125 Vac

Insulation: Receptacles

Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

7503BK-SP-C

Switch Deco 3Way 15A 120/277V BK Can

UPC: 032664643781

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade
Special Features: Flush, Non-Grounding
Application: Commercial grade
Standard: UL
Number Of Poles: 3
Number Of Wires: 3
Wire Size: 4 AWG
Amperage Rating: 50 Amp
Voltage Rating: 125/250 Vac
Material: High Strength Glass Reinforced Nylon
Color: Brown
NEMA Rating: 10-50R
Mounting: Flush
Connection: Plug
Size: 1.81 X 2.50 X 3.28 IN
Environmental Conditions: See Spec Sheet
Dielectric Strength: 125/250 Vac
Insulation: Receptacles
Temperature Rating: -20C to 70C (-4F to 158F)

7503GY-BOX

Switch Decorator 3Way 15A 120/277V GY

UPC: 032664627873

Brand Name: Eaton
Sub Brand: EATON
Type: Snap-N- Receptacles
Special Features: Straight Body, Wiring Type Back Wire
Application: Snap In Receptacles
Number Of Poles: 2
Number Of Wires: 3
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Cord Type: 1.07 In Diameter
Material: Quick Connect With Wire Lead, Grounding, Snap In Clamps, Wire Leads
Color: Black/White
NEMA Rating: 5-15P
Connection: Snap-N
Size: 0.19 X 0.65 X 0.74 X 0.94 X 1.04 X 1.22
Environmental Conditions: -40 To 65 Deg C



Powering Business Worldwide

7503LA

Switch Decorator 3Way 15A 120/277V LA

UPC: 032664627668

Brand Name: Cooper Wiring Devices

Type: Rectangular, Straight Blade

Special Features: With Solder Connect, Slotted Terminal

Application: Commercial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Urea Face, Polypropylene Base

Color: Black

NEMA Rating: 5-15R

Mounting: Snap-In

7503LA-BOX

Switch Decorator 3Way 15A 120/277V LA

UPC: 032664627811

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Single, Straight Blade

Special Features:

Application: Commercial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Urea Face, Polypropylene Base

Color: Black

NEMA Rating: 5-15R

Mounting: Snap In

Connection: Quick Connect

Dielectric Strength: 2000 V



Powering Business Worldwide

7503V

Switch Decorator 3Way 15A 120/277V IV

UPC: 032664627699

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Plastic Back and Clips, Solder Connect, Slotted Terminals

Application: Commercial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Urea Face, Polypropylene Base

Color: Black

NEMA Rating: 5-15R

Mounting: Snap-In

Connection: Quick Connect, Wire Lead

7503V-BOX

Switch Decorator 3Way 15A 120/277V IV

UPC: 032664627828

Brand Name: Eaton

Sub Brand: ARROW HART

Special Features:

Application: Standard

Voltage Rating: 125 Vac

Amperage Rating: 15 Amp

Connection: Screw

Actuator: Toggle

Color: Ivory

Contact Configuration: Receptacle

Size: 4270V W/Flush Strap & NO Mounting Screws

Mounting: Wall

Operating Temperature: -20 To 60 Deg C



Powering Business Worldwide

7503V-C

Switch Deco 3Way 15A 120/277V IV Can_n

UPC: 032664643484

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Single, Straight Blade, Square_n
Special Features: Fiber Back and Steel Clips
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 12 AWG
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Material: Urea Face, Polypropylene Base
Color: Black
NEMA Rating: 5-15R
Mounting: Snap-In
Connection: Quick Connect, Wire Lead

7503V-JP;51

7503V Sold in Boxes of 10 Can

UPC: 032664643606

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade, Square
Special Features: Fiber Back and Steel Clips
Application: Snap-in rcpts
Standard: UL
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 12 AWG
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Material: Urea Face, Polypropylene Base
Color: White
NEMA Rating: 5-15R
Mounting: Snap-In
Connection: Quick Connect, Wire Lead
Size: 1.81 X 2.50 X 3.28 IN
Environmental Conditions: See Spec Sheet
Dielectric Strength: 2000 V
Insulation: Urea Face, Polypropylene Base
Temperature Rating: -20C to 70C (-4F to 158F)



Powering Business Worldwide

7503W

Switch Decorator 3Way 15A 120/277V WH

UPC: 032664627729

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Single, Straight Blade, Square

Special Features:

Application: Commercial

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 12 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Urea Face, Polypropylene Base

Color: Black

NEMA Rating: 5-15R

Connection: Wire Lead

Dielectric Strength: 2000 V

7503W-BOX

Switch Decorator 3Way 15A 120/277V WH

UPC: 032664627835

7503W-C

Switch Deco 3Way 15A 120/277V WH Can

UPC: 032664643491



Powering Business Worldwide

7503W-JP;51

7503W Sold in Boxes of 10 Can

UPC: 032664643620

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Single, Straight Blade, Square
Special Features: Fiber Back and Steel Clips
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 12 AWG
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Material: Urea Face, Polypropylene Base
Color: Black
NEMA Rating: 5-15R
Mounting: Snap-In
Connection: 90 Deg Quick Connect, Wire Lead

C7503V-SP

Switch Deco 3Way 15A 120/277V W/Wlpt IV

UPC: 032664644214

Brand Name: Cooper Wiring Devices
Type: 3 Speed Fan Control, 3-Way
Voltage Rating: 120 Vac
Amperage Rating: 1.5 Amp
Number Of Poles: 1
Frequency Rating: 60 Hz
Material: Polycarbonate
Operating Temperature: 0 To 40 Deg C