



Powering Business Worldwide

### 7503A-C

Switch Deco 3Way 15A 120/277V AL Can

UPC: 032664643477

### 7503B-BOX

Switch Decorator 3Way 15A 120/277V BR

UPC: 032664627804

### 7503BK-BOX

Switch Decorator 3Way 15A 120/277V BK

UPC: 032664627866

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Standard Grade, High Impact Resistant, Wiring Type Push

Application: Commercial grade

Standard: UL

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Impact Resistant Thermoplastic

Color: Black

NEMA Rating: 5-15R

Mounting: Flush

Connection: Screw

Size: 1.31 In Width X 0.69 In Depth X 4.19 In Height

Environmental Conditions: See Spec Sheet

Dielectric Strength: 125 Vac

Insulation: Receptacles

Temperature Rating: -20C to 70C (-4F to 158F)