



Powering Business Worldwide

7503BK-SP-C

Switch Deco 3Way 15A 120/277V BK Can

UPC: 032664643781

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single, Straight Blade
Special Features: Flush, Non-Grounding
Application: Commercial grade
Standard: UL
Number Of Poles: 3
Number Of Wires: 3
Wire Size: 4 AWG
Amperage Rating: 50 Amp
Voltage Rating: 125/250 Vac
Material: High Strength Glass Reinforced Nylon
Color: Brown
NEMA Rating: 10-50R
Mounting: Flush
Connection: Plug
Size: 1.81 X 2.50 X 3.28 IN
Environmental Conditions: See Spec Sheet
Dielectric Strength: 125/250 Vac
Insulation: Receptacles
Temperature Rating: -20C to 70C (-4F to 158F)

7503GY-BOX

Switch Decorator 3Way 15A 120/277V GY

UPC: 032664627873

Brand Name: Eaton
Sub Brand: EATON
Type: Snap-N- Receptacles
Special Features: Straight Body, Wiring Type Back Wire
Application: Snap In Receptacles
Number Of Poles: 2
Number Of Wires: 3
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Cord Type: 1.07 In Diameter
Material: Quick Connect With Wire Lead, Grounding, Snap In Clamps, Wire Leads
Color: Black/White
NEMA Rating: 5-15P
Connection: Snap-N
Size: 0.19 X 0.65 X 0.74 X 0.94 X 1.04 X 1.22
Environmental Conditions: -40 To 65 Deg C