



Powering Business Worldwide

7504A-BOX

Switch Decorator 4Way 15A 120/277V AL

UPC: 032664644665

Brand Name: Cooper Wiring Devices
Sub Brand: ARROW HART
Type: Single, Straight Blade, Square
Special Features: Fiber Back and Steel Clips
Application: Commercial
Number Of Poles: 2
Number Of Wires: 3
Wire Size: 14 To 12 AWG
Amperage Rating: 15 Amp
Voltage Rating: 125 Vac
Material: Urea Face, Polypropylene Base
Color: Black
NEMA Rating: 5-15R
Mounting: Snap-In
Connection: 90 Deg Quick Connect, Wire Lead

7504B-BOX

Switch Decorator 4Way 15A 120/277V BR

UPC: 032664644672

Brand Name: Eaton
Sub Brand: ARROW HART
Type: Single & Duplex Receptacles
Special Features: Wiring Type Back Wire and Side Wire
Application: Commercial grade
Standard: UL
Number Of Poles: 3
Number Of Wires: 4
Wire Size: 4 AWG
Amperage Rating: 50 Amp
Voltage Rating: 125/250 Vac
Material: Nylon
Color: Black
NEMA Rating: 14-50R
Mounting: Panel
Connection: Screw
Size: 2.01 X 2.09 X 2.50 X 4.75IN
Environmental Conditions: Indoor
Dielectric Strength: 125/250 Vav
Insulation: Nylon Face
Temperature Rating: -20C to 70C (-4F to 158F)