



Powering Business Worldwide

### 9504SG

Switch Aspire 4Way 15A 120/277V SG

UPC: 032664645532

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Hospital,GFCI,Back And Side Wire

Special Features: Hospital Grade, Tamper Resistant, Wiring Type Back and Side Wire, With Standard Size Unbreakable Wallplate

Application: Hospital Grade

Voltage Rating: 125 Vac

Amperage Rating: 15 Amp

Number Of Poles: 2 Pole/ 3 Wire

Enclosure: Hospital Grade Tamper Resistant

Connection: Screw

Material: Nylon Top Housing, Polycarbonate Bottom Housing

Width: 1.3

### 9504WS

Switch Aspire 4Way 15A 120/277V WS

UPC: 032664645549

Brand Name: Eaton

Sub Brand: ARROW HART

Type: Hospital,GFCI,Back And Side Wire

Special Features: Hospital Grade, Tamper Resistant, Wiring Type Back and Side Wire, With Standard Size Unbreakable Wallplate

Application: Hospital Grade

Voltage Rating: 125 Vac

Amperage Rating: 15 Amp

Number Of Poles: 2 Pole/ 3 Wire

Enclosure: Hospital Grade Tamper Resistant

Connection: Screw

Material: Nylon Top Housing, Polycarbonate Bottom Housing

Width: 1.3