



Hospital grade straight blade duplex receptacles

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Description

2-Pole, 3-Wire Grounding
 15A 125V/AC;
 20A 125V/AC
 NEMA 5-15, 5-20



8200



TR8300



Design features

- Tapered back wiring lead-in slots assist in gathering stranded wires for faster, more secure connections
- Long, broad mounting strap helps reach large panel cutouts for code compliance
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure, provides redundant measure of ground continuity where jumper used
- All terminal and mounting screws triple combination (Slot/Phillips/Robertson) head for maximum installer flexibility
- Screw-Catch feature on duplex devices speeds mounting of wallplates

Table 1. Hospital Grade Receptacles, Back & Side Wire

Catalog No.	Description	Amps	Volts	Color Suffix
□ 8200__	NEMA 5-15R Duplex Receptacle, Back & Side Wire	15	125	B, GY, RD, V, W
□ 8300__	NEMA 5-20R Duplex Receptacle, Back & Side Wire	20	125	B, GY, LA, RD, V, W

Table 2. Hospital Grade Tamper Resistant Receptacles, Back & Side Wire

Catalog No.	Description	Amps	Volts	Color Suffix
□ TR8200__	NEMA 5-15R Duplex Receptacle, Back & Side Wire	15	125	GY, RD, V, W
□ TR8300__	NEMA 5-20R Duplex Receptacle, Back & Side Wire	20	125	B, GY, RD, V, W

Compliances, specifications and availability are subject to change without notice.



Powering Business Worldwide

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Applications

Arrow Hart's feature-rich line of hospital grade receptacles have been designed to meet and exceed the demanding requirements of UL498 and Federal Specification WC-596G to provide a consistent means of connectivity where downtime can be crucial. Features include high-impact and chemical-resistant faces to withstand abuse and maintain structural integrity plus durable contact designs for long life blade retention. The entire line of hospital grade receptacles fulfill the requirements for long-term reliability, low maintenance and assured performance.

Table 3. Specifications

Catalog No.	8200, 8300 Series	TR8200, TR8300 Series
Device Type	Hospital Grade Duplex Receptacles	Tamper Resistant Hospital Grade Duplex Receptacles
Wiring Type	Back & side wire	Back & side wire
Testing & Code Compliance	<ul style="list-style-type: none"> Listed to UL 498, file no. E15058 UL verified to Federal Spec. WC-596G CSA certified to C22.2, no. 42, file no. 6914 (6233-01) NOM certified 	<ul style="list-style-type: none"> cULus Listed to UL 498, file no. E15058 UL verified to Federal Spec. WC-596G NOM certified
Environmental Specifications	Flammability: Meets UL 94 requirements; V2 rated Temperature Rating: -20°C to 90°C (-4°F to 194°F).	Flammability: Meets UL 94 requirements; V2 rated Temperature Rating: -20°C to 90°C (-4°F to 194°F)
Electrical Specifications	Dielectric Voltage: Withstands 2000V per UL 498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)	Dielectric Voltage: Withstands 2000V per UL 498 Current Interrupting: Yes, at full-rated current Temperature Rise: Max. 30°C (86°F) after 250 cycles of overload @ 200% of rated current (DC)
Mechanical Specifications	Terminal Accommodation: #14 - 10 AWG Voltage Ratings: N/A	Terminal Accommodation: #14 - 10 AWG Voltage Ratings: N/A

Table 4. Materials

Catalog No.	8200, 8300 Series	TR8200, TR8300 Series
Face	Nylon	Nylon
Base	PVC	PVC
Strap	0.046" thick steel, zinc plated	0.046" thick steel, zinc plated
Auto Ground	Phosphor bronze staple	Phosphor bronze staple
Line Contacts	0.030" thick 3-leaf brass	0.037" thick 3-leaf brass
Ground Contact	Riveted	Riveted
Terminal Screws	#8-32 steel, brass plated, hot neutral screw nickel plated	#8-32 steel, brass plated, hot neutral screw nickel plated
Ground Screw	#8-32 steel, zinc plated (green)	#8-32 steel, zinc plated (green)
Tamper Resistant Shutters	N/A	Reliable Delrin® shutter assembly

Table 5. Color Ordering Information

For ordering devices, include Cat. No. followed by the color code: B (Brown), GY (Gray), LA (Lt. Almond), RD (Red), V (Ivory), W (White)

B	GY	LA	RD	V	W
Brown	Gray	Lt. Almond	Red	Ivory	White

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Product Dimensions




Figure 1. 8200 Line Art with Dimensions




Figure 2. 8300 Line Art with Dimensions




Figure 3. TR8200 Line Art with Dimensions












Figure 4. TR8300 Line Art with Dimensions

Technical Data


Effective October 2014

Project Name:	Prepared By:
Project Number:	Date:
Catalog Number:	Type:

Certifications & Compliances

Catalog No.								
8200
8300
TR8200
TR8300

KEY:  cULus  UL  Fed Spec  CSA
 NOM  Arrowlink  Build-To-Spec  ROHS

 Parts are manufactured and designed in accordance with article 4 of the European Union's RoHS2 directive 2011/65/EU

 Build-To-Spec Customizable Devices

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Cooperwiringdevices.com

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Cooperwiringdevices.com

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 178 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Cooperwiringdevices.com

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2014 Eaton
All Rights Reserved
Printed in USA
Publication No. E125-0145-14
October 2014

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.