

CR Series

Product Summary

Product	Replaces
CR4™ - 4" LED Recessed Downlights	
CR4-575L 575Lm, 2700K, E26 Base, 9.5W	15W CFL 50W BR INCANDESCENT
CR4-575L-GU24 575Lm, 2700K, GU24 Base, 9.5W	15W CFL 50W BR INCANDESCENT
CR4-575L-D 575Lm, 2700K, E26 Base, 9.5W, Chrome painted reflector	15W CFL 50W BR INCANDESCENT
CR4-575L-GU24-D 575Lm, 2700K, GU24 Base, 9.5W, Chrome painted reflector	15W CFL 50W BR INCANDESCENT
CR6™ - 6" LED Recessed Downlights	
CR6-625L 625Lm, 2700K, E26 Base, 9.5W	18W CFL 65W INCANDESCENT
CR6-625L-GU24 625Lm, 2700K, GU24 Base, 9.5W	18W CFL 65W INCANDESCENT
CR6-800L 800Lm, 2700K, E26 Base, 12W	26W CFL 90W PAR INCANDESCENT
CR6-800L-GU24 800Lm, 2700K, GU24 Base, 12W	26W CFL 90W PAR INCANDESCENT

Extended

Product Offering



LR Series

- Equivalent up to 32W CFL
- 6" aperture with multiple reflector depths
- **Efficacy:** 90 LPW
- **Delivered Light Output:** Up to 1000 lumens at 11W
- Multiple CCTs at 90 CRI
- Available in 120V or 277V
- **Dimming (LR6, 120V):** Dimmable to 20%
- **Dimming (LR6-10L, 120V):** Dimmable to 5%

LR4™

- Equivalent up to 50W Incandescent
- 4" aperture with spun aluminum reflectors
- **Delivered Light Output:** Up to 540 lumens
- **Input Power:** 10.5W
- Multiple CCTs at 90 CRI
- **Dimming:** Dimmable to 20%
- Available in 120V only

LE6™

- **Utilizes Cree TrueWhite® Technology**
- Active Color Management
- **Delivered Light Output:** 500 lumens (at 30° tilt)
- **Input Power:** 12 watts
- **CRI:** 90
- **CCT:** 2700K, 3500K
- **Lifetime:** Designed to last 50,000 hours
- **Dimming:** Dimmable to 20%
- **Warranty:** 5 years