



Representative

**Catalog Number:** TR63  
**Product ID:** 7TAA267170R0022  
**UPC Number:** 78378610146  
**Status:** Active

Aluminum 4-1/4 inch Service Entrance Compression Splice for Wire Range 4 ASCR, 4 Str., 2 Sol., Orange, Die: 5/8

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Connector
Special Features	Contains Oxide Inhibiting Compound
Application	Semi-tension Splice used for Service Entrance on Commercial-Industrial Loads
Standard	Passes the requirements of ANSI C119.4
Size	4-1/4 inch
Connection	Crimp/ Compression
Conductor Range	4 ASCR, 4 Stranded, 2 Solid.
Number Of Conductors	2
Material	Aluminum
Insulation	None
Mounting	None
Environmental Conditions	All Seasons / Conditions

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	6.8x5.3x4.69
Outer Quantity	400
Outer Dimensions (inches)	20.4x11.6x7.8
Weight Uom	11.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)