

CS Series Accessories

Mounting Options for CS Series Linear Luminaires

Qty.	AC5-12/3-48-Q14B-JB 5" Cable Canopy with 48" #12/3 SJT Cord, Q14B Gripper, J-box strap	Qty.	AC5-18/5-48-Q14B-JB 5" Cable Canopy with 48" #18/5 SJT Cord, Q14B Gripper, J-box strap	Qty.	AC5-18/2-48-Q14B-JB 5" Cable Canopy with 48" #18/2 SVT Cord, Q14B Gripper, J-box strap
	<p>Bracket w/ 1" 1/4-20 Stud & Ground Screw</p> <p>Ø5" White Ceiling Canopy</p> <p>Stop Sleeve</p> <p>Slip Ring Cable Coupler</p> <p>Strain Relief Bushing</p> <p>White #12/3 SJT Power Cord*</p> <p>48"</p> <p>1/16" Galvanized 7x7 Cable</p> <p>Cable Tie (1 per foot)</p> <p>1/4 IPS Lock Nut</p> <p>Cable Gripper Q14B</p> <p>Both Ends Prepped</p> <p>*Cable Length + 6.0" MIN 90° C SUPPLY CONDUCTORS MAX 20 AMPS</p> <p>Power Feed with Cable Support for use with single or row mounted luminaires for non-dimming applications.</p>		<p>Bracket w/ 1" 1/4-20 Stud & Ground Screw</p> <p>Ø5" White Ceiling Canopy</p> <p>Stop Sleeve</p> <p>Slip Ring Cable Coupler</p> <p>Strain Relief Bushing</p> <p>White #18/5 Power & 0-10V Control SJT Cord*</p> <p>48"</p> <p>1/16" Galvanized 7x7 Cable</p> <p>Cable Tie (1 per foot)</p> <p>1/4 IPS Lock Nut</p> <p>Cable Gripper Q14B</p> <p>Both Ends Prepped</p> <p>*Cable Length + 6.0" MIN 90° C SUPPLY CONDUCTORS MAX 10 AMPS</p> <p>Power Feed with Cable Support for use with single or row mounted luminaires for dimming applications.</p>		<p>Bracket w/ 1" 1/4-20 Stud & Ground Screw</p> <p>Ø5" White Ceiling Canopy</p> <p>Stop Sleeve</p> <p>Slip Ring Cable Coupler</p> <p>Strain Relief Bushing</p> <p>White #18/2 0-10V SVT Control Cord*</p> <p>48"</p> <p>1/16" Galvanized 7x7 Cable</p> <p>Cable Tie (1 per foot)</p> <p>1/4 IPS Lock Nut</p> <p>Cable Gripper Q14B</p> <p>Strain Relief Bushing SR-1241-W</p> <p>Both Ends Prepped</p> <p>*Cable Length + 6.0" MIN 90° C SUPPLY CONDUCTORS</p> <p>Dimming Control with Cable Support for use with Power Feed AC5-12/3-48-Q14B-JB for selective luminaire dimming control in row configurations.</p>

Ordering Information

Enter Custom Orders Below

Qty.	Type	Power Drop	Length	Connector to Luminaire	Connector to Ceiling	Options
	AC5 Adjustable Cable 5" Canopy	Blank No Power Drop Provided	# Cable Length in 24-inch increments (48" or 24" standard as shown)	Blank No Connector Provided Q14B 1/4 IP Gripper (bottom feed) CC Cable Coupler	JB J-Box Strap Provided TB T-Bar Clamp Provided (not for use when power drops are provided)	Blank Color: White
	AC2 Adjustable Cable 2" Canopy (power drop not available)	12/3 3#12 SJT Power Cord Provided (Max. Power: 20 amps)				
	PC5 Adjustable Power Cord 5" Canopy (no aircraft cable)	18/5 5#18 SJT Power & 0-10V Cord Provided (Max. Power: 10 amps) 18/2 2#18 SVT 0-10V Cord Provided				
	AC Adjustable Cable (no canopy)	Blank No Power Drop Provided			LP Cable Loop Provided	Blank Color: White
	TM Plastic Tong Hanger (24-pack) Pair supplied with each fixture.					
	TMM Metal Tong Hanger (pair). Recommended for surface mount.					
	CSESK Electrical Starter Kit (50-Pack)					

Maximum number of allowable luminaires connected to a single Power Feed:

12AWG Input Power Feed on 20 amp circuit (limited to 16A per NEC)		18AWG Input Power Feed on 10 amp circuit (limited to 8A per NEC)	
4' Fixtures: 120V: 43 fixtures 277V: 100 fixtures	8' Fixtures: 120V: 23 fixtures 277V: 53 fixtures	4' Fixtures: 120V: 21 fixtures 277V: 50 fixtures	8' Fixtures: 120V: 11 fixtures 277V: 26 fixtures

Rev. Date 11/29/2012



CS Series Accessories

<p>Qty. AC5-48-Q14B-TB 5" Cable Canopy , 48" Cable, Q14B Gripper, T-bar clip</p> <p>AC5-48-Q14B-TB-50BULK 5" Cable Canopy , 48" Cable, Q14B Gripper, T-bar clip (50-Bulk Pack)</p>	<p>Qty. AC2-48-Q14B-TB 2" Cable Canopy , 48" Cable, Q14B Gripper, T-bar clip</p> <p>AC2-48-Q14B-JB-50BULK 2" Cable Canopy , 48" Cable, Q14B Gripper, T-bar clip (50-Bulk Pack)</p>	<p>Qty. AC-144-Q14B-LP Adjustable 144" Loop Cable with Q14B Gripper</p> <p>AC-144-Q14B-LP-50BULK Adjustable 144" Loop Cable with Q14B Gripper (50-Bulk Pack)</p>
<p>Qty. PC5-12/3-24-JB 5" Canopy with 24" #12/3 SJT Cord, J-box strap</p>	<p>Qty. PC5-18/5-24-JB 5" Canopy with 24" #18/5 SJT Cord, J-box strap</p>	<p>Qty. PC5-18/2-24-JB 5" Canopy with 24" #18/2 SVT Cord, J-box strap</p>
<p>*Cable Length + 6.0" MIN 90°C SUPPLY CONDUCTORS MAX 20 AMPS</p> <p>Power Feed with for use with single or row mounted luminaires for non-dimming applications.</p>	<p>*Cable Length + 6.0" MIN 90°C SUPPLY CONDUCTORS MAX 10 AMPS</p> <p>Power Feed for use with single or row mounted luminaires for dimming applications.</p>	<p>*Cable Length + 6.0" MIN 90°C SUPPLY CONDUCTORS MAX 10 AMPS</p> <p>Dimming Control for use with Power Feed PC5-12/3-24-JB for selective luminaire dimming control in row configurations.</p>
<p>Qty. TM Plastic Tong Hanger (Pair)</p>	<p>Qty. TMM Metal Tong Hanger (Pair)</p>	<p>Qty. CSESK Electrical Starter Kit (50-Pack) Optional</p>