

LR6-10L

Six-Inch LED Downlight

Product Description

The LR6-10L LED downlight delivers 1000 lumens of exceptional 90+ CRI light while achieving 90 lumens per watt. This breakthrough performance is achieved by combining the high efficacy and high-quality light of Cree TrueWhite[®] Technology, with an integrated driver and thermal management design. The LR6-10L is available in warm or neutral color temperatures and has a variety of trim options. It easily installs into Cree six-inch GU24 housings or may be retrofitted with a GU24 whip adapter, making the LR6-10L perfect for use in commercial new construction or retrofit applications.

Performance Summary

Utilizes Cree TrueWhite [®] Technology
Active Color Management
Delivered Light Output: 1000 lumens
Input Power: 11 watts
CRI: 90
CCT: 2700K, 3500K
Warranty: 5 years
Lifetime: Designed to last 50,000 hours
Dimming: Dimmable to 5%*

Housings & Accessories

Reference Housing & Accessory documents for more details.

Trims	
LT6A-DR Diffuse anodized finish	LT6AB-DR Black anodized finish
LT6AW-DR Wheat diffuse anodized finish	LT6WH-DR Smooth white
LT6AP-DR Pewter diffuse anodized finish	LT6BB-DR Flat black finish trim and reflector

Housings (GU24 Only)	
H6 Architectural	SC6 Cylindrical Surface Mount
RC6 New Construction	SC6-CM Cylindrical Cord Mount
RR6 Retrofit	SC6-WM Cylindrical Wall Mount

Ordering Information

Example: LR6-10L-35K-120V-DR

LR6	10L		120V	DR
Series	Lumen Output	Color Temperature	Voltage	Options
LR6	10L 11W 1000 lumens - 90 LPW	27K 2700 Kelvin 35K 3500 Kelvin	120V 120 Volts - GU24 Base	DR Deep Recess - 20° Shield

* Reference www.cree.com/lighting for recommended dimmers.

LR6-10L

