




WALL MOUNT LIGHT DUTY SERIES: 48.00" x 23.25" x 24.00"
 PART NO.: WLR48AKP1VVV3

REVISIONS			
REV	ECO	DATE	DESCRIPTION
--	--	--	--


MOUNTING RAILS: 26U
 10-32 TAPPED RAIL, 26U
 (1) PAIR, 19" EIA-310-D COMPLIANT
 20PC HARDWARE INCLUDED
 ADJUSTABLE FRONT-BACK
 MAX. EQ. DEPTH: 18.00"




TOP/BTM VIEW
 VENTED, 2-FAN READY
 CABLE KNOCK-OUTS




FRONT VIEW



SIDE VIEW



REAR VIEW
 OPEN SUB-PANEL
 MOUNTING DIMS:
 45.25 x 12.00
 45.25 x 16.00



DIMENSIONS

WALL MOUNT
 LIGHT WEIGHT
 HEIGHT: 48.00"
 WIDTH: 23.25"
 DEPTH: 24.00"

WT CAPACITY
 125 LBS. STATIC CAP.

BOX

VENTED SIDES
 VENTED TOP
 VENTED BOTTOM

FRONT DOOR

PLEXIGLASS, RECESSED
 DIM: 46"Hx20"Wx0.50"D

MOUNTING RAIL

L-TYPE RAILS
 10-32 (26U)
 10-32 HARDWARE PACK
 19" RACKABLE
 ADJUSTABLE UP TO 18"

REAR PANEL

4" DEEP SUB-PANEL
 DIM: 48"Hx23.25"Wx4"D
 3.00" KNOCK-OUTS
 0.88" KNOCK-OUTS

ACCESSORIES

* 20PC HARDWARE PACK (1x)

COLOR

BLACK TEXTURED
 EPOXY POWDER-COAT

DAMAC
 PRODUCTS INC.
 LA MIRADA, CA 90638

ALL INFORMATION ARE PROPRIETARY DATA OF DAMAC PRODUCTS INC. ANY REPRODUCTION/USE IN ANY FORM MUST HAVE PRIOR WRITING AGREEMENT W/ DAMAC.
 TOLERANCE .XXX" .010 ".XX" .030 ".X .060 "(DEG) .5
 ALL DIM. ARE IN INCHES UNLESS OTHERWISE SPECIFIED.

WALL MOUNT, LIGHT DUTY
 48.00 x 23.25 x 24.00
 W/ 10- 32 TAPPED RAILS

PART NO.
 WLR48AKP1VVV3
 DRAWN BY: AP
 DATE: 08.17.2010

CHECKED BY: CR
 SCALE: N/A
 SHEET: 1 OF 1
 REV: --

MATERIAL: N/A
 FINISH: EPOXY POWDER-COAT
 MAX BEND R=.030, RELIEF=.060 A/R.
 UNLESS OTHERWISE SPECIFIED