

[-Click to Print-](#)

You are here: [Home](#) > [Incandescent](#) > [Incandescent Bulbs](#) > [CFC](#) > 00127A

ITEM#: 00127A



Item#:	00127A
Industry Desc.:	25CFC 32MM
Volts:	130
Watts:	25
Avg. Life Hours:	3,000
Mean Lumens:	137@120V 180@130V
Shape:	Flame
Base Type:	E12 Candelabra Screw
Finish:	Clear
CRI:	100
MOL:	4.06 in. (103.12 mm.)
Diameter:	1.25 in. (31.75 mm.)
Package Qty:	25
Case Qty:	500