

[-Click to Print-](#)

You are here: [Home](#) > [Incandescent](#) > [Incandescent Bulbs](#) > [A19](#) > 00350D

ITEM#: 00350D



Item#:	00350D
Industry Desc.:	100ARS
Volts:	130
Watts:	100
Avg. Life Hours:	4,000
Initial Lumens:	1200
Shape:	A19
Base Type:	E26 Medium Screw
Finish:	Frost
Kelvin:	2850
MOL:	4.34 in. (110.24 mm.)
Diameter:	2.36 in. (59.94 mm.)
Package Qty:	4
Case Qty:	120
Additional Info:	ROUGH SERVICE 5 SUPPORTS