

[-Click to Print-](#)

You are here: [Home](#) > [H.I.D.](#) > [Metal Halide](#) > [Open Rated](#) > 01060F

ITEM#: 01060F



Item#: 01060F
Industry Desc.: MP1000W/BU/4K
Watts: 1000
Avg. Life Hours: 11,000
Shape: BT56
Base Type: EX39 Excl. Mogul
Base Material: Nickel Plated Brass
Finish: Clear
Package Qty: 1
Case Qty: 6

Additional Info: ANSI M47 BALLAST
THIS OPEN RATED METAL HALIDE LAMP IS DESIGNED TO MEET
CURRENT NEC REQUIREMENTS FOR OPERATION IN OPEN
FIXTURES. THIS LAMP IS DESIGNED TO HELP CONTAIN HOT
PARTICLES IN THE EVENT OF AN ARC TUBE RUPTURE.