

[-Click to Print-](#)

You are here: [Home](#) > [H.I.D.](#) > [High Pressure Sodium](#) > [ED 23.5](#) > 01072D

**ITEM#: 01072D**



**Item#:** 01072D  
**Industry Desc.:** LU70/ECO  
**Watts:** 70  
**Avg. Life Hours:** 24,000+  
**Shape:** ED23 1/2  
**Base Type:** E39 Mogul Screw  
**Finish:** Clear  
**CRI:** 22  
**MOL:** 7.50 in. (190.50 mm.)  
**Package Qty:** 1  
**Case Qty:** 12  
**Additional Info:** ANSI BALLAST TYPE S62

This lamp passes the Toxicity Characteristic Leaching Procedure (TCLP) as set forth in ANSI standard C78.LL 1256-2003.