

[-Click to Print-](#)

You are here: [Home](#) > [Incandescent](#) > [Incandescent Bulbs](#) > [A19](#) > 02026A

ITEM#: 02026A



[Additional Images](#)

[Spec Image](#)

| | |
|-------------------------|--------------------------|
| Item#: | 02026A |
| Industry Desc.: | 60A19CL/RS ROUGH SERVICE |
| Volts: | 130 |
| Watts: | 60 |
| Avg. Life Hours: | 4,000 |
| Shape: | A19 |
| Base Type: | E26 Medium Screw |
| Finish: | Clear |
| Kelvin: | 2850 |
| MOL: | 4.00 in. (101.60 mm.) |
| Diameter: | 2.30 in. (58.42 mm.) |
| Package Qty: | 4 |
| Case Qty: | 120 |
| Additional Info: | ROUGH SERVICE 5 SUPPORTS |