

[-Click to Print-](#)

You are here: [Home](#) > [Incandescent](#) > [Incandescent Bulbs](#) > [A19](#) > 02027A

ITEM#: 02027A



Item#:	02027A
Industry Desc.:	100A19CLRS ROUGH SERVICE
Volts:	130
Watts:	100
Avg. Life Hours:	4,000
Shape:	A19
Base Type:	E26 Medium Screw
Finish:	Clear
Kelvin:	2850
MOL:	4.35 in. (110.49 mm.)
Diameter:	2.40 in. (60.96 mm.)
Package Qty:	4
Case Qty:	120
Additional Info:	ROUGH SERVICE 5 SUPPORTS