

[-Click to Print-](#)

You are here: [Home](#) > [H.I.D.](#) > [Metal Halide](#) > [Enclosed Rated](#) > 05250A

ITEM#: 05250A



Item#: 05250A
Industry Desc.: M100W/U/MED/PS/4K
Watts: 100
Avg. Life Hours: 15,000/11,250
Shape: ED17
Base Type: E26 Medium Screw
Finish: Clear
Kelvin: 4000
CRI: 65
Package Qty: 1
Case Qty: 12
Additional Info: /4k White color with increased visual color rendering. Great for general purpose applications. Pulse start.

This lamp is not designed for use in open fixtures. Burn this lamp only in enclosed fixtures. Please refer to our "MP" protectant Metal Halide line for lamps designed for open fixtures. Look at the description.