

[-Click to Print-](#)

You are here: [Home](#) > [Tungsten Halogen\(Quartz\)](#) > [Tungsten Halogen Bulbs Medium](#) > [Par38](#) > 05714A

**ITEM#: 05714A**



**Item#:** 05714A  
**Industry Desc.:** 90PAR38QFL/33/SS  
**Volts:** 130  
**Watts:** 90  
**Avg. Life Hours:** 2,500  
**Initial Lumens:** 1275  
**Shape:** PAR38  
**Base Type:** E26 Medium Screw  
**Base Material:** Nickel Plated Brass  
**BeamSpread:** 33  
**Finish:** Clear  
**Package Qty:** 1  
**Case Qty:** 12  
**Additional Info:** SAFE-SHIELD  
SILICONE RUBBER COATED  
SHATTER RESISTANT  
5,000 Average Life Hours @ 120V  
Suitable for use in wet location or outdoor applications only when installed in fixtures that are certified by Underwriters Laboratories under UL Standard 1598 as being suitable for use in wet location or outdoor applications respectively.  
Suitable for use in residential/commercial.